

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211577

Luminaire Tested: **LE\_4B20D010 EC4B10208030 4LBS1WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211577  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B20D010 EC4B10208030 4LBS1WH  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2319.8 lumens  
Efficiency: N/A  
Efficacy: 111.5 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211577

CATALOG NUMBER: LE\_4B20D010 EC4B10208030 4LBS1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P211577

CATALOG NUMBER: LE\_4B20D010 EC4B10208030 4LBS1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89				89
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77				77
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67				67
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59				59
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52				52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47				47
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42				42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35				35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211577

CATALOG NUMBER: LE\_4B20D010 EC4B10208030 4LBS1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.6	5.5
10°-20°	330.3	14.2
20°-30°	432.0	18.6
30°-40°	457.5	19.7
40°-50°	426.7	18.4
50°-60°	323.1	13.9
60°-70°	175.0	7.5
70°-80°	46.9	2.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	889.9	38.4
0°-40°	1347.4	58.1
0°-60°	2097.2	90.4
0°-90°	2319.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2319.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1384	
5°	1363	128
15°	1180	330
25°	939	432
35°	731	457
45°	556	427
55°	363	323
65°	175	175
75°	41	47
85°	0	1
90°	0	



TEST NUMBER: P211577

CATALOG NUMBER: LE\_4B20D010 EC4B10208030 4LBS1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1383.5
2.5°	1378.4
5°	1363.2
7.5°	1330.2
10°	1287.0
12.5°	1236.3
15°	1180.4
17.5°	1117.0
20°	1061.2
22.5°	997.7
25°	939.3
27.5°	880.9
30°	825.0
32.5°	776.9
35°	731.1
37.5°	685.4
40°	642.3
42.5°	599.1
45°	556.0
47.5°	507.7
50°	459.5
52.5°	411.2
55°	363.0
57.5°	312.3
60°	264.0
62.5°	218.3
65°	175.2
67.5°	134.6
70°	98.9
72.5°	68.6
75°	40.6
77.5°	17.7
80°	5.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)