

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210826

Luminaire Tested: **LSR4B10D010BZ EC4B10208030 4LBWGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P210826  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B10D010BZ EC4B10208030 4LBWGPH1  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 702.7 lumens  
Efficiency: N/A  
Efficacy: 71.0 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210826

CATALOG NUMBER: LSR4B10D010BZ EC4B10208030 4LBWGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P210826

CATALOG NUMBER: LSR4B10D010BZ EC4B10208030 4LBWGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92			92																
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83																
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76			76																
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69			69																
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63																
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57			57																
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53			53																
8	73	62	56	51	72	62	55	51	61	55	51	59	54	50	58	54	50	48			48																
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			45																
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41			41																

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P210826

CATALOG NUMBER: LSR4B10D010BZ EC4B10208030 4LBWGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.7	6.8
10°-20°	135.2	19.2
20°-30°	193.9	27.6
30°-40°	182.6	26.0
40°-50°	100.8	14.3
50°-60°	32.3	4.6
60°-70°	8.1	1.2
70°-80°	1.9	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	376.8	53.6
0°-40°	559.4	79.6
0°-60°	692.5	98.6
0°-90°	702.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	702.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	506	
5°	503	48
15°	479	135
25°	425	194
35°	296	183
45°	128	101
55°	33	32
65°	7	8
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P210826

CATALOG NUMBER: LSR4B10D010BZ EC4B10208030 4LBWGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	505.8
2.5°	502.1
5°	503.3
7.5°	499.7
10°	493.6
12.5°	487.5
15°	479.0
17.5°	471.6
20°	459.5
22.5°	442.4
25°	425.3
27.5°	402.2
30°	371.7
32.5°	337.6
35°	296.2
37.5°	252.3
40°	207.2
42.5°	165.7
45°	128.0
47.5°	96.3
50°	69.5
52.5°	48.7
55°	32.9
57.5°	21.9
60°	15.8
62.5°	11.0
65°	7.3
67.5°	4.9
70°	3.7
72.5°	2.4
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)