

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210864

Luminaire Tested: **LSR4B10D010BZ EC4B10209730 4LBMGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P210864  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B10D010BZ EC4B10209730 4LBMGPH1  
Description: PORTFOLIO 4 INCH CYLINDER  
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 432.6 lumens  
Efficiency: N/A  
Efficacy: 43.7 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210864

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBMGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P210864

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBMGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93		
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86		
3	102	95	90	86	100	93	89	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73		
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68		
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51		
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P210864

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBMGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.9	9.5
10°-20°	106.7	24.7
20°-30°	136.9	31.6
30°-40°	99.0	22.9
40°-50°	35.5	8.2
50°-60°	9.6	2.2
60°-70°	3.1	0.7
70°-80°	0.9	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	284.5	65.8
0°-40°	383.5	88.7
0°-60°	428.5	99.1
0°-90°	432.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	432.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	445	
5°	437	41
15°	380	107
25°	302	137
35°	158	99
45°	43	35
55°	10	10
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P210864

CATALOG NUMBER: LSR4B10D010BZ EC4B10209730 4LBMGPH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	444.8
2.5°	442.9
5°	436.6
7.5°	426.6
10°	412.9
12.5°	397.5
15°	380.2
17.5°	362.9
20°	345.6
22.5°	325.6
25°	302.0
27.5°	274.7
30°	240.1
32.5°	200.1
35°	158.3
37.5°	120.1
40°	87.3
42.5°	61.8
45°	42.7
47.5°	29.1
50°	19.1
52.5°	13.6
55°	10.0
57.5°	7.3
60°	5.5
62.5°	4.5
65°	2.7
67.5°	1.8
70°	1.8
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)