

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211629

Luminaire Tested: **LE_4B20D010 EC4B10209730 4LBPS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10209730 4LBPS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1869.7 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211629

CATALOG NUMBER: LE_4B20D010 EC4B10209730 4LBPS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211629

CATALOG NUMBER: LE_4B20D010 EC4B10209730 4LBPS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211629

CATALOG NUMBER: LE_4B20D010 EC4B10209730 4LBPS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.4	3.8
10°-20°	203.5	10.9
20°-30°	306.4	16.4
30°-40°	364.6	19.5
40°-50°	363.9	19.5
50°-60°	295.9	15.8
60°-70°	182.1	9.7
70°-80°	70.6	3.8
80°-90°	11.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	581.2	31.1
0°-40°	945.9	50.6
0°-60°	1605.7	85.9
0°-90°	1869.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1869.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	753	
5°	751	71
15°	722	203
25°	667	306
35°	584	365
45°	473	364
55°	331	296
65°	183	182
75°	64	71
85°	9	11
90°	0	



TEST NUMBER: P211629

CATALOG NUMBER: LE_4B20D010 EC4B10209730 4LBPS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	753.3
2.5°	754.3
5°	751.1
7.5°	746.7
10°	741.1
12.5°	731.1
15°	722.3
17.5°	709.0
20°	694.6
22.5°	681.3
25°	666.9
27.5°	646.9
30°	627.0
32.5°	608.2
35°	583.8
37.5°	557.3
40°	532.8
42.5°	503.0
45°	473.0
47.5°	440.9
50°	406.6
52.5°	371.1
55°	331.2
57.5°	292.4
60°	254.7
62.5°	218.2
65°	182.8
67.5°	149.5
70°	118.6
72.5°	89.8
75°	64.3
77.5°	42.1
80°	25.5
82.5°	15.5
85°	8.8
87.5°	4.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)