

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211755

Luminaire Tested: **LE\_4B20D010 EC4B10209040 4L1BWH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211755  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B20D010 EC4B10209040 4L1BWH  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1703.6 lumens  
Efficiency: N/A  
Efficacy: 81.9 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211755

CATALOG NUMBER: LE\_4B20D010 EC4B10209040 4L1BWH

### Luminous Intensity Polar Plot





TEST NUMBER: P211755

CATALOG NUMBER: LE\_4B20D010 EC4B10209040 4L1BWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82				82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61				61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55				55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50				50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46				46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43				43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39				39

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211755

CATALOG NUMBER: LE\_4B20D010 EC4B10209040 4L1BWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.6	6.1
10°-20°	301.3	17.7
20°-30°	444.6	26.1
30°-40°	438.8	25.8
40°-50°	268.5	15.8
50°-60°	102.9	6.0
60°-70°	32.1	1.9
70°-80°	9.4	0.6
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	850.5	49.9
0°-40°	1289.3	75.7
0°-60°	1660.7	97.5
0°-90°	1703.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1703.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1098	
5°	1098	105
15°	1068	301
25°	973	445
35°	712	439
45°	344	269
55°	109	103
65°	30	32
75°	9	9
85°	0	1
90°	0	



TEST NUMBER: P211755

CATALOG NUMBER: LE\_4B20D010 EC4B10209040 4L1BWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1098.1
2.5°	1100.4
5°	1098.1
7.5°	1095.7
10°	1088.8
12.5°	1079.6
15°	1068.0
17.5°	1054.1
20°	1033.3
22.5°	1010.2
25°	973.2
27.5°	927.0
30°	869.2
32.5°	797.5
35°	712.0
37.5°	617.2
40°	520.1
42.5°	430.0
45°	344.4
47.5°	268.2
50°	203.5
52.5°	150.2
55°	108.7
57.5°	76.3
60°	55.4
62.5°	41.6
65°	30.0
67.5°	23.1
70°	16.1
72.5°	11.6
75°	9.3
77.5°	4.6
80°	4.6
82.5°	2.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)