

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211017

Luminaire Tested: **LSR4B10D010BZ EC4B10208050 4LBNI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211017
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10208050 4LBNI1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 818.8 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211017

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBNLI1

Luminous Intensity Polar Plot





TEST NUMBER: P211017

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 |
| 1 | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 95 | | | 95 |
| 2 | 109 | 105 | 102 | 99 | 107 | 103 | 100 | 98 | 100 | 98 | 95 | 97 | 95 | 93 | 95 | 93 | 92 | 90 | | | 90 |
| 3 | 105 | 99 | 95 | 92 | 103 | 98 | 94 | 91 | 95 | 92 | 89 | 93 | 90 | 88 | 91 | 89 | 87 | 85 | | | 85 |
| 4 | 101 | 94 | 89 | 86 | 99 | 93 | 88 | 85 | 91 | 87 | 84 | 89 | 86 | 83 | 87 | 84 | 82 | 81 | | | 81 |
| 5 | 96 | 89 | 84 | 80 | 95 | 88 | 84 | 80 | 87 | 82 | 79 | 85 | 81 | 79 | 83 | 80 | 78 | 77 | | | 77 |
| 6 | 92 | 85 | 80 | 76 | 91 | 84 | 79 | 76 | 83 | 78 | 75 | 81 | 78 | 75 | 80 | 77 | 74 | 73 | | | 73 |
| 7 | 89 | 81 | 76 | 72 | 88 | 80 | 75 | 72 | 79 | 75 | 71 | 78 | 74 | 71 | 77 | 73 | 71 | 69 | | | 69 |
| 8 | 85 | 77 | 72 | 68 | 84 | 77 | 72 | 68 | 76 | 71 | 68 | 75 | 71 | 68 | 74 | 70 | 67 | 66 | | | 66 |
| 9 | 82 | 74 | 69 | 65 | 81 | 73 | 68 | 65 | 72 | 68 | 65 | 72 | 68 | 65 | 71 | 67 | 64 | 63 | | | 63 |
| 10 | 79 | 71 | 66 | 62 | 78 | 70 | 65 | 62 | 69 | 65 | 62 | 69 | 65 | 62 | 68 | 64 | 62 | 61 | | | 61 |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211017

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBNLI1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 166.1 | 20.3 |
| 10°-20° | 284.3 | 34.7 |
| 20°-30° | 225.9 | 27.6 |
| 30°-40° | 119.6 | 14.6 |
| 40°-50° | 20.6 | 2.5 |
| 50°-60° | 1.6 | 0.2 |
| 60°-70° | 0.8 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 676.3 | 82.6 |
| 0°-40° | 795.8 | 97.2 |
| 0°-60° | 818.0 | 99.9 |
| 0°-90° | 818.8 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 818.8 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2107 | |
| 5° | 1889 | 166 |
| 15° | 1028 | 284 |
| 25° | 487 | 226 |
| 35° | 189 | 120 |
| 45° | 21 | 21 |
| 55° | 1 | 2 |
| 65° | 1 | 1 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P211017

CATALOG NUMBER: LSR4B10D010BZ EC4B10208050 4LBNLI1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2107.1 |
| 2.5° | 2052.9 |
| 5° | 1889.0 |
| 7.5° | 1674.6 |
| 10° | 1447.6 |
| 12.5° | 1228.2 |
| 15° | 1027.7 |
| 17.5° | 841.1 |
| 20° | 692.3 |
| 22.5° | 578.8 |
| 25° | 486.7 |
| 27.5° | 412.3 |
| 30° | 337.9 |
| 32.5° | 262.3 |
| 35° | 189.1 |
| 37.5° | 124.8 |
| 40° | 74.4 |
| 42.5° | 42.9 |
| 45° | 21.4 |
| 47.5° | 7.6 |
| 50° | 2.5 |
| 52.5° | 2.5 |
| 55° | 1.3 |
| 57.5° | 1.3 |
| 60° | 1.3 |
| 62.5° | 1.3 |
| 65° | 1.3 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)