

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211046

Luminaire Tested: **LSR4B10D010BZ EC4B10209050 4LBNI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211046
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209050 4LBNI1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 688.7 lumens
Efficiency: N/A
Efficacy: 69.6 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211046

CATALOG NUMBER: LSR4B10D010BZ EC4B10209050 4LBNLI1

Luminous Intensity Polar Plot





TEST NUMBER: P211046

CATALOG NUMBER: LSR4B10D010BZ EC4B10209050 4LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.7	20.3
10°-20°	239.1	34.7
20°-30°	190.0	27.6
30°-40°	100.6	14.6
40°-50°	17.3	2.5
50°-60°	1.3	0.2
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	568.8	82.6
0°-40°	669.4	97.2
0°-60°	688.0	99.9
0°-90°	688.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	688.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1772	
5°	1589	140
15°	864	239
25°	409	190
35°	159	101
45°	18	17
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P211046

CATALOG NUMBER: LSR4B10D010BZ EC4B10209050 4LBNLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1772.2
2.5°	1726.6
5°	1588.7
7.5°	1408.4
10°	1217.5
12.5°	1033.0
15°	864.3
17.5°	707.4
20°	582.2
22.5°	486.8
25°	409.4
27.5°	346.8
30°	284.2
32.5°	220.6
35°	159.1
37.5°	105.0
40°	62.6
42.5°	36.1
45°	18.0
47.5°	6.4
50°	2.1
52.5°	2.1
55°	1.1
57.5°	1.1
60°	1.1
62.5°	1.1
65°	1.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)