

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211055

Luminaire Tested: **LSR4B10D010BZ EC4B10209050 4LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211055
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209050 4LBSWH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 923.8 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211055

CATALOG NUMBER: LSR4B10D010BZ EC4B10209050 4LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P211055

CATALOG NUMBER: LSR4B10D010BZ EC4B10209050 4LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77																			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67																			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59																			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211055

CATALOG NUMBER: LSR4B10D010BZ EC4B10209050 4LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.8	5.5
10°-20°	131.5	14.2
20°-30°	172.0	18.6
30°-40°	182.1	19.7
40°-50°	169.9	18.4
50°-60°	128.7	13.9
60°-70°	69.7	7.5
70°-80°	18.7	2.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	354.4	38.4
0°-40°	536.5	58.1
0°-60°	835.1	90.4
0°-90°	923.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	923.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	551	
5°	543	51
15°	470	132
25°	374	172
35°	291	182
45°	221	170
55°	145	129
65°	70	70
75°	16	19
85°	0	0
90°	0	



TEST NUMBER: P211055

CATALOG NUMBER: LSR4B10D010BZ EC4B10209050 4LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	551.0
2.5°	548.9
5°	542.9
7.5°	529.7
10°	512.5
12.5°	492.3
15°	470.1
17.5°	444.8
20°	422.6
22.5°	397.3
25°	374.0
27.5°	350.8
30°	328.5
32.5°	309.3
35°	291.1
37.5°	272.9
40°	255.8
42.5°	238.6
45°	221.4
47.5°	202.2
50°	183.0
52.5°	163.8
55°	144.6
57.5°	124.3
60°	105.1
62.5°	86.9
65°	69.8
67.5°	53.6
70°	39.4
72.5°	27.3
75°	16.2
77.5°	7.1
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)