

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211062

Luminaire Tested: **LSR4B10D010BZ EC4B10209050 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209050 4LBWWH1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 811.7 lumens
Efficiency: N/A
Efficacy: 82.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211062

CATALOG NUMBER: LSR4B10D010BZ EC4B10209050 4LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P211062

CATALOG NUMBER: LSR4B10D010BZ EC4B10209050 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|-----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 70 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | 100 | | | | | | | | | | | | | | | | | |
| 1 | 113 | 110 | 107 | 104 | 110 | 107 | 105 | 103 | 103 | 101 | 100 | 100 | 98 | 97 | 96 | 95 | 94 | 92 | | | | | | | | | | | 92 | | | | | | | | | | | | | | | | | |
| 2 | 106 | 101 | 96 | 92 | 104 | 99 | 95 | 91 | 96 | 92 | 89 | 93 | 90 | 87 | 90 | 87 | 85 | 84 | | | | | | | | | | | 84 | | | | | | | | | | | | | | | | | |
| 3 | 100 | 93 | 87 | 82 | 98 | 91 | 86 | 82 | 88 | 84 | 80 | 86 | 82 | 79 | 84 | 80 | 78 | 76 | | | | | | | | | | | 76 | | | | | | | | | | | | | | | | | |
| 4 | 94 | 85 | 79 | 74 | 92 | 84 | 78 | 74 | 82 | 77 | 73 | 80 | 75 | 72 | 78 | 74 | 71 | 69 | | | | | | | | | | | 69 | | | | | | | | | | | | | | | | | |
| 5 | 88 | 79 | 72 | 67 | 86 | 78 | 71 | 67 | 76 | 70 | 66 | 74 | 69 | 65 | 72 | 68 | 65 | 63 | | | | | | | | | | | 63 | | | | | | | | | | | | | | | | | |
| 6 | 83 | 73 | 66 | 61 | 81 | 72 | 65 | 61 | 70 | 64 | 60 | 69 | 64 | 60 | 67 | 63 | 59 | 58 | | | | | | | | | | | 58 | | | | | | | | | | | | | | | | | |
| 7 | 78 | 67 | 60 | 56 | 76 | 67 | 60 | 55 | 65 | 59 | 55 | 64 | 59 | 55 | 63 | 58 | 54 | 53 | | | | | | | | | | | 53 | | | | | | | | | | | | | | | | | |
| 8 | 73 | 62 | 56 | 51 | 72 | 62 | 55 | 51 | 61 | 55 | 51 | 60 | 54 | 50 | 59 | 54 | 50 | 49 | | | | | | | | | | | 49 | | | | | | | | | | | | | | | | | |
| 9 | 69 | 58 | 51 | 47 | 68 | 58 | 51 | 47 | 57 | 51 | 47 | 56 | 50 | 47 | 55 | 50 | 46 | 45 | | | | | | | | | | | 45 | | | | | | | | | | | | | | | | | |
| 10 | 65 | 54 | 48 | 43 | 64 | 54 | 48 | 43 | 53 | 47 | 43 | 52 | 47 | 43 | 51 | 46 | 43 | 41 | | | | | | | | | | | 41 | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211062

CATALOG NUMBER: LSR4B10D010BZ EC4B10209050 4LBWWH1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 49.2 | 6.1 |
| 10°-20° | 152.1 | 18.7 |
| 20°-30° | 234.0 | 28.8 |
| 30°-40° | 225.8 | 27.8 |
| 40°-50° | 117.7 | 14.5 |
| 50°-60° | 24.8 | 3.1 |
| 60°-70° | 5.7 | 0.7 |
| 70°-80° | 2.2 | 0.3 |
| 80°-90° | 0.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 435.3 | 53.6 |
| 0°-40° | 661.1 | 81.4 |
| 0°-60° | 803.6 | 99.0 |
| 0°-90° | 811.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 811.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 508 | |
| 5° | 512 | 49 |
| 15° | 538 | 152 |
| 25° | 513 | 234 |
| 35° | 366 | 226 |
| 45° | 150 | 118 |
| 55° | 22 | 25 |
| 65° | 5 | 6 |
| 75° | 2 | 2 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P211062

CATALOG NUMBER: LSR4B10D010BZ EC4B10209050 4LBWWH1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 507.5 |
| 2.5° | 508.6 |
| 5° | 511.8 |
| 7.5° | 516.0 |
| 10° | 522.4 |
| 12.5° | 530.9 |
| 15° | 538.3 |
| 17.5° | 542.6 |
| 20° | 539.4 |
| 22.5° | 533.0 |
| 25° | 512.8 |
| 27.5° | 488.4 |
| 30° | 456.6 |
| 32.5° | 414.1 |
| 35° | 366.3 |
| 37.5° | 314.3 |
| 40° | 260.1 |
| 42.5° | 206.0 |
| 45° | 149.7 |
| 47.5° | 100.9 |
| 50° | 64.8 |
| 52.5° | 39.3 |
| 55° | 22.3 |
| 57.5° | 13.8 |
| 60° | 9.6 |
| 62.5° | 7.4 |
| 65° | 5.3 |
| 67.5° | 4.2 |
| 70° | 3.2 |
| 72.5° | 3.2 |
| 75° | 2.1 |
| 77.5° | 1.1 |
| 80° | 1.1 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)