

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211130

Luminaire Tested: **LSR4B15D010BZ EC4B10209027 4LBNB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211130
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209027 4LBNB1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 476.5 lumens
Efficiency: N/A
Efficacy: 33.3 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211130

CATALOG NUMBER: LSR4B15D010BZ EC4B10209027 4LBNB1

Luminous Intensity Polar Plot





TEST NUMBER: P211130

CATALOG NUMBER: LSR4B15D010BZ EC4B10209027 4LBNB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.9	13.6
10°-20°	137.7	28.9
20°-30°	159.8	33.5
30°-40°	100.0	21.0
40°-50°	14.1	3.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	362.4	76.1
0°-40°	462.4	97.0
0°-60°	476.5	100.0
0°-90°	476.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	476.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	779	
5°	722	65
15°	489	138
25°	353	160
35°	160	100
45°	12	14
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P211130

CATALOG NUMBER: LSR4B15D010BZ EC4B10209027 4LBNB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	779.1
2.5°	763.8
5°	722.0
7.5°	662.0
10°	600.7
12.5°	542.2
15°	489.2
17.5°	444.6
20°	411.2
22.5°	380.5
25°	352.6
27.5°	319.2
30°	276.0
32.5°	221.6
35°	160.3
37.5°	104.5
40°	59.9
42.5°	30.7
45°	12.5
47.5°	2.8
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)