

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211819

Luminaire Tested: **LE_4B30D010 EC4B30509024 4LBCS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211819
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509024 4LBCS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2552.4 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211819

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBCS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211819

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBCS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211819

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBCS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	3.9
10°-20°	281.2	11.0
20°-30°	423.0	16.6
30°-40°	501.3	19.6
40°-50°	498.9	19.5
50°-60°	402.2	15.8
60°-70°	243.3	9.5
70°-80°	90.3	3.5
80°-90°	13.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	803.0	31.5
0°-40°	1304.3	51.1
0°-60°	2205.3	86.4
0°-90°	2552.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2552.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1042	
5°	1038	99
15°	996	281
25°	919	423
35°	803	501
45°	650	499
55°	449	402
65°	244	243
75°	82	90
85°	11	13
90°	0	



TEST NUMBER: P211819

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBCS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1042.5
2.5°	1042.5
5°	1037.9
7.5°	1034.7
10°	1025.4
12.5°	1010.0
15°	996.1
17.5°	980.7
20°	962.1
22.5°	943.5
25°	918.7
27.5°	892.5
30°	863.0
32.5°	835.2
35°	802.7
37.5°	768.7
40°	728.5
42.5°	689.9
45°	649.6
47.5°	604.7
50°	555.3
52.5°	504.3
55°	448.6
57.5°	399.0
60°	343.4
62.5°	293.8
65°	244.4
67.5°	198.0
70°	154.6
72.5°	116.0
75°	82.0
77.5°	52.5
80°	31.0
82.5°	18.6
85°	10.8
87.5°	4.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)