

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211259

Luminaire Tested: **LSR4B15D010BZ EC4B10209730 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211259
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209730 4LBSWMH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1111.0 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211259

CATALOG NUMBER: LSR4B15D010BZ EC4B10209730 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P211259

CATALOG NUMBER: LSR4B15D010BZ EC4B10209730 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211259

CATALOG NUMBER: LSR4B15D010BZ EC4B10209730 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.1	5.9
10°-20°	172.5	15.5
20°-30°	231.6	20.8
30°-40°	237.1	21.3
40°-50°	205.2	18.5
50°-60°	136.5	12.3
60°-70°	56.0	5.0
70°-80°	6.7	0.6
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	469.2	42.2
0°-40°	706.3	63.6
0°-60°	1048.0	94.3
0°-90°	1111.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1111.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	704	
5°	693	65
15°	616	172
25°	505	232
35°	379	237
45°	267	205
55°	152	137
65°	55	56
75°	3	7
85°	0	0
90°	0	



TEST NUMBER: P211259

CATALOG NUMBER: LSR4B15D010BZ EC4B10209730 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	704.1
2.5°	702.7
5°	693.2
7.5°	678.7
10°	659.0
12.5°	637.2
15°	616.0
17.5°	589.1
20°	562.9
22.5°	535.2
25°	505.4
27.5°	473.3
30°	441.3
32.5°	409.2
35°	378.7
37.5°	349.5
40°	321.9
42.5°	294.2
45°	267.2
47.5°	238.8
50°	209.7
52.5°	180.6
55°	151.5
57.5°	126.0
60°	99.8
62.5°	75.7
65°	55.3
67.5°	36.4
70°	21.1
72.5°	10.2
75°	2.9
77.5°	1.5
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)