

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211288

Luminaire Tested: **LSR4B15D010BZ EC4B10208035 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211288
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35087)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10208035 4LBSWMH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1525.7 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211288

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P211288

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 102 | 100 | 97 | 98 | 96 | 94 | 95 | 93 | 92 | 90 |
| 2 | 104 | 98 | 92 | 88 | 102 | 96 | 91 | 87 | 92 | 88 | 85 | 89 | 86 | 83 | 86 | 84 | 81 | 79 |
| 3 | 96 | 88 | 82 | 76 | 94 | 87 | 81 | 76 | 84 | 79 | 74 | 81 | 77 | 73 | 79 | 75 | 72 | 70 |
| 4 | 90 | 80 | 73 | 67 | 88 | 79 | 72 | 67 | 76 | 70 | 66 | 74 | 69 | 65 | 72 | 68 | 64 | 62 |
| 5 | 83 | 73 | 65 | 59 | 82 | 72 | 64 | 59 | 70 | 63 | 59 | 68 | 62 | 58 | 66 | 61 | 57 | 56 |
| 6 | 78 | 66 | 59 | 53 | 76 | 65 | 58 | 53 | 64 | 57 | 53 | 62 | 57 | 52 | 61 | 56 | 52 | 50 |
| 7 | 73 | 61 | 53 | 48 | 71 | 60 | 53 | 48 | 59 | 52 | 48 | 57 | 52 | 47 | 56 | 51 | 47 | 45 |
| 8 | 68 | 56 | 49 | 44 | 67 | 56 | 48 | 43 | 54 | 48 | 43 | 53 | 47 | 43 | 52 | 47 | 43 | 41 |
| 9 | 64 | 52 | 45 | 40 | 63 | 52 | 45 | 40 | 50 | 44 | 40 | 49 | 44 | 39 | 49 | 43 | 39 | 38 |
| 10 | 60 | 48 | 41 | 37 | 59 | 48 | 41 | 37 | 47 | 41 | 36 | 46 | 40 | 36 | 45 | 40 | 36 | 35 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 119275 |
| 5° | 117874 |
| 10° | 113350 |
| 15° | 108031 |
| 20° | 101465 |
| 25° | 94451 |
| 30° | 86311 |
| 35° | 78300 |
| 40° | 71169 |
| 45° | 64018 |
| 50° | 55265 |
| 55° | 44730 |
| 60° | 33797 |
| 65° | 22181 |
| 70° | 10459 |
| 75° | 1906 |
| 80° | 710 |
| 85° | 0 |



TEST NUMBER: P211288

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBSWMH1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 89.4 | 5.9 |
| 10°-20° | 236.8 | 15.5 |
| 20°-30° | 318.1 | 20.8 |
| 30°-40° | 325.6 | 21.3 |
| 40°-50° | 281.8 | 18.5 |
| 50°-60° | 187.4 | 12.3 |
| 60°-70° | 77.0 | 5.0 |
| 70°-80° | 9.2 | 0.6 |
| 80°-90° | 0.4 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 644.3 | 42.2 |
| 0°-40° | 969.9 | 63.6 |
| 0°-60° | 1439.2 | 94.3 |
| 0°-90° | 1525.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1525.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 967 | |
| 5° | 952 | 89 |
| 15° | 846 | 237 |
| 25° | 694 | 318 |
| 35° | 520 | 326 |
| 45° | 367 | 282 |
| 55° | 208 | 187 |
| 65° | 76 | 77 |
| 75° | 4 | 9 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P211288

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-----|
| 0° | 967 |
| 2.5° | 965 |
| 5° | 952 |
| 7.5° | 932 |
| 10° | 905 |
| 12.5° | 875 |
| 15° | 846 |
| 17.5° | 809 |
| 20° | 773 |
| 22.5° | 735 |
| 25° | 694 |
| 27.5° | 650 |
| 30° | 606 |
| 32.5° | 562 |
| 35° | 520 |
| 37.5° | 480 |
| 40° | 442 |
| 42.5° | 404 |
| 45° | 367 |
| 47.5° | 328 |
| 50° | 288 |
| 52.5° | 248 |
| 55° | 208 |
| 57.5° | 173 |
| 60° | 137 |
| 62.5° | 104 |
| 65° | 76 |
| 67.5° | 50 |
| 70° | 29 |
| 72.5° | 14 |
| 75° | 4 |
| 77.5° | 2 |
| 80° | 1 |
| 82.5° | 1 |
| 85° | 0 |
| 87.5° | 0 |
| 90° | 0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)