

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211830

Luminaire Tested: **LE\_4B30D010 EC4B30509024 4LBN1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211830  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B30D010 EC4B30509024 4LBN1MW  
Description: PORTFOLIO 4 INCH CYLINDER  
NARROW DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1745.1 lumens  
Efficiency: N/A  
Efficacy: 62.3 lumens/watt  
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211830

CATALOG NUMBER: LE\_4B30D010 EC4B30509024 4LBN1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P211830

CATALOG NUMBER: LE\_4B30D010 EC4B30509024 4LBN1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	105	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	80	96	89	83	79	86	82	78	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	62	57	53	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	53	49	58	53	49	48			
9	69	58	51	46	68	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211830

CATALOG NUMBER: LE\_4B30D010 EC4B30509024 4LBN1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	137.0	7.8
10°-20°	358.3	20.5
20°-30°	471.6	27.0
30°-40°	367.2	21.0
40°-50°	178.3	10.2
50°-60°	112.6	6.5
60°-70°	72.7	4.2
70°-80°	38.0	2.2
80°-90°	9.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	966.9	55.4
0°-40°	1334.1	76.4
0°-60°	1625.0	93.1
0°-90°	1745.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1745.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1489	
5°	1461	137
15°	1278	358
25°	1040	472
35°	588	367
45°	222	178
55°	125	113
65°	72	73
75°	36	38
85°	8	9
90°	0	



TEST NUMBER: P211830

CATALOG NUMBER: LE\_4B30D010 EC4B30509024 4LBN1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1488.7
2.5°	1480.4
5°	1461.0
7.5°	1427.7
10°	1383.4
12.5°	1333.5
15°	1278.1
17.5°	1219.9
20°	1158.8
22.5°	1100.6
25°	1039.6
27.5°	962.0
30°	856.7
32.5°	731.8
35°	587.8
37.5°	454.7
40°	352.1
42.5°	274.5
45°	221.8
47.5°	180.1
50°	158.0
52.5°	141.4
55°	124.7
57.5°	110.9
60°	97.0
62.5°	83.2
65°	72.0
67.5°	63.8
70°	52.7
72.5°	44.3
75°	36.1
77.5°	27.7
80°	19.4
82.5°	13.8
85°	8.4
87.5°	2.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)