

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211844

Luminaire Tested: **LE_4B30D010 EC4B30509024 4LBW1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211844
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509024 4LBW1MW
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2136.3 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211844

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211844

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78		
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69		
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61		
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55		
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50		
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45		
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211844

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.5	5.7
10°-20°	339.9	15.9
20°-30°	480.4	22.5
30°-40°	465.3	21.8
40°-50°	314.0	14.7
50°-60°	194.8	9.1
60°-70°	130.2	6.1
70°-80°	71.3	3.3
80°-90°	18.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	941.8	44.1
0°-40°	1407.1	65.9
0°-60°	1916.0	89.7
0°-90°	2136.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2136.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1295	
5°	1283	122
15°	1206	340
25°	1053	480
35°	748	465
45°	402	314
55°	213	195
65°	130	130
75°	67	71
85°	17	19
90°	0	



TEST NUMBER: P211844

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1294.6
2.5°	1294.6
5°	1283.4
7.5°	1269.6
10°	1253.0
12.5°	1236.3
15°	1205.8
17.5°	1180.9
20°	1139.4
22.5°	1097.7
25°	1053.4
27.5°	992.4
30°	925.9
32.5°	840.0
35°	748.4
37.5°	657.0
40°	565.5
42.5°	474.0
45°	401.9
47.5°	335.5
50°	285.5
52.5°	243.9
55°	213.4
57.5°	188.5
60°	169.1
62.5°	149.6
65°	130.3
67.5°	113.7
70°	97.0
72.5°	83.2
75°	66.6
77.5°	52.7
80°	38.9
82.5°	27.7
85°	16.6
87.5°	5.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)