

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211328

Luminaire Tested: **LSR4B15D010BZ EC4B10208040 4LBMGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211328  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B15D010BZ EC4B10208040 4LBMGPH1  
Description: PORTFOLIO 4 INCH CYLINDER  
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W  
DL3-15.28W DLE-15.432W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 836.3 lumens  
Efficiency: N/A  
Efficacy: 58.5 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211328

CATALOG NUMBER: LSR4B15D010BZ EC4B10208040 4LBMGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P211328

CATALOG NUMBER: LSR4B15D010BZ EC4B10208040 4LBMGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93						93													
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86						86													
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79						79													
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73						73													
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68						68													
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63						63													
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59						59													
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55						55													
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51						51													
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48						48													

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211328

CATALOG NUMBER: LSR4B15D010BZ EC4B10208040 4LBMGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.1	9.5
10°-20°	206.3	24.7
20°-30°	264.6	31.6
30°-40°	191.3	22.9
40°-50°	68.6	8.2
50°-60°	18.5	2.2
60°-70°	6.1	0.7
70°-80°	1.9	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	550.0	65.8
0°-40°	741.3	88.6
0°-60°	828.3	99.1
0°-90°	836.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	836.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	860	
5°	844	79
15°	735	206
25°	584	265
35°	306	191
45°	83	69
55°	19	19
65°	5	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P211328

CATALOG NUMBER: LSR4B15D010BZ EC4B10208040 4LBMGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	859.7
2.5°	856.2
5°	843.9
7.5°	824.6
10°	798.2
12.5°	768.3
15°	734.9
17.5°	701.5
20°	668.1
22.5°	629.4
25°	583.7
27.5°	530.9
30°	464.1
32.5°	386.8
35°	305.9
37.5°	232.1
40°	168.8
42.5°	119.6
45°	82.6
47.5°	56.3
50°	36.9
52.5°	26.4
55°	19.3
57.5°	14.1
60°	10.5
62.5°	8.8
65°	5.3
67.5°	3.5
70°	3.5
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)