

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211861

Luminaire Tested: **LE_4B30D010 EC4B30508027 4LBPS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211861
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508027 4LBPS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3452.6 lumens
Efficiency: N/A
Efficacy: 123.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211861

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBPS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211861

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBPS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211861

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBPS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.8	3.8
10°-20°	375.7	10.9
20°-30°	565.8	16.4
30°-40°	673.2	19.5
40°-50°	672.0	19.5
50°-60°	546.6	15.8
60°-70°	336.3	9.7
70°-80°	130.2	3.8
80°-90°	20.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1073.3	31.1
0°-40°	1746.6	50.6
0°-60°	2965.2	85.9
0°-90°	3452.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3452.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1391	
5°	1387	132
15°	1334	376
25°	1232	566
35°	1078	673
45°	874	672
55°	612	547
65°	338	336
75°	119	130
85°	16	21
90°	0	



TEST NUMBER: P211861

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBPS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1391.1
2.5°	1393.0
5°	1386.9
7.5°	1378.8
10°	1368.6
12.5°	1350.1
15°	1333.8
17.5°	1309.2
20°	1282.6
22.5°	1258.0
25°	1231.5
27.5°	1194.7
30°	1157.8
32.5°	1123.0
35°	1078.1
37.5°	1028.9
40°	983.9
42.5°	928.7
45°	873.5
47.5°	814.2
50°	750.8
52.5°	685.3
55°	611.7
57.5°	540.1
60°	470.5
62.5°	403.0
65°	337.6
67.5°	276.2
70°	218.9
72.5°	165.6
75°	118.7
77.5°	77.7
80°	47.1
82.5°	28.7
85°	16.4
87.5°	8.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)