

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211867

Luminaire Tested: **LE_4B30D010 EC4B30508027 4LBS1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508027 4LBS1WH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3197.6 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211867

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1WH

Luminous Intensity Polar Plot





TEST NUMBER: P211867

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211867

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.9	5.5
10°-20°	455.3	14.2
20°-30°	595.5	18.6
30°-40°	630.6	19.7
40°-50°	588.1	18.4
50°-60°	445.4	13.9
60°-70°	241.2	7.5
70°-80°	64.7	2.0
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1226.7	38.4
0°-40°	1857.2	58.1
0°-60°	2890.8	90.4
0°-90°	3197.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3197.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1907	
5°	1879	176
15°	1627	455
25°	1295	595
35°	1008	631
45°	766	588
55°	500	445
65°	241	241
75°	56	65
85°	0	1
90°	0	



TEST NUMBER: P211867

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1907.0
2.5°	1900.1
5°	1879.1
7.5°	1833.6
10°	1774.1
12.5°	1704.2
15°	1627.1
17.5°	1539.7
20°	1462.6
22.5°	1375.2
25°	1294.7
27.5°	1214.2
30°	1137.3
32.5°	1070.8
35°	1007.8
37.5°	944.8
40°	885.3
42.5°	825.8
45°	766.3
47.5°	699.8
50°	633.4
52.5°	566.9
55°	500.4
57.5°	430.4
60°	363.9
62.5°	300.9
65°	241.4
67.5°	185.5
70°	136.4
72.5°	94.4
75°	56.0
77.5°	24.5
80°	7.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)