

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211377

Luminaire Tested: **LSR4B15D010BZ EC4B10209040 4LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211377
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209040 4LBWGPH1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 849.3 lumens
Efficiency: N/A
Efficacy: 59.4 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211377

CATALOG NUMBER: LSR4B15D010BZ EC4B10209040 4LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P211377

CATALOG NUMBER: LSR4B15D010BZ EC4B10209040 4LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92																			
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76																			
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69																			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63																			
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57																			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53																			
8	73	62	56	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48																			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45																			
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211377

CATALOG NUMBER: LSR4B15D010BZ EC4B10209040 4LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.7	6.8
10°-20°	163.4	19.2
20°-30°	234.3	27.6
30°-40°	220.6	26.0
40°-50°	121.9	14.4
50°-60°	39.1	4.6
60°-70°	9.8	1.2
70°-80°	2.3	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	455.4	53.6
0°-40°	676.0	79.6
0°-60°	837.0	98.6
0°-90°	849.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	849.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	611	
5°	608	58
15°	579	163
25°	514	234
35°	358	221
45°	155	122
55°	40	39
65°	9	10
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P211377

CATALOG NUMBER: LSR4B15D010BZ EC4B10209040 4LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	611.3
2.5°	606.8
5°	608.3
7.5°	603.9
10°	596.5
12.5°	589.2
15°	578.9
17.5°	570.0
20°	555.3
22.5°	534.7
25°	514.0
27.5°	486.1
30°	449.2
32.5°	408.0
35°	357.9
37.5°	304.9
40°	250.4
42.5°	200.3
45°	154.7
47.5°	116.4
50°	84.0
52.5°	58.9
55°	39.8
57.5°	26.5
60°	19.1
62.5°	13.3
65°	8.8
67.5°	5.9
70°	4.4
72.5°	2.9
75°	1.5
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)