

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211869

Luminaire Tested: **LE_4B30D010 EC4B30508027 4LBW1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211869
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508027 4LBW1B
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1583.0 lumens
Efficiency: N/A
Efficacy: 56.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211869

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBW1B

Luminous Intensity Polar Plot





TEST NUMBER: P211869

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	70	89	80	74	70	79	73	69	77	72	69	75	71	68	67	67	67	67
6	85	76	69	65	84	75	69	64	73	68	64	72	67	64	70	66	63	62	62	62	62
7	80	71	64	60	79	70	64	59	69	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53	53	53	53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	68	58	52	48	67	58	52	48	57	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211869

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	7.9
10°-20°	353.5	22.3
20°-30°	488.6	30.9
30°-40°	418.4	26.4
40°-50°	177.8	11.2
50°-60°	19.9	1.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	966.9	61.1
0°-40°	1385.3	87.5
0°-60°	1583.0	100.0
0°-90°	1583.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1583.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1321	
5°	1314	125
15°	1255	354
25°	1072	489
35°	679	418
45°	224	178
55°	11	20
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P211869

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1321.4
2.5°	1317.8
5°	1314.0
7.5°	1306.7
10°	1292.0
12.5°	1284.7
15°	1255.4
17.5°	1229.6
20°	1189.2
22.5°	1141.6
25°	1071.8
27.5°	994.7
30°	906.7
32.5°	800.2
35°	679.1
37.5°	554.2
40°	429.4
42.5°	319.3
45°	223.9
47.5°	139.4
50°	80.7
52.5°	40.4
55°	11.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)