

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211383

Luminaire Tested: **LSR4B15D010BZ EC4B10208050 4LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211383
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10208050 4LBCSMMS1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1364.8 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211383

CATALOG NUMBER: LSR4B15D010BZ EC4B10208050 4LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P211383

CATALOG NUMBER: LSR4B15D010BZ EC4B10208050 4LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76	76	76	76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65	65	65	65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50	50	50	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44	44	44	44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40	40	40	40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36	36	36	36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32	32	32	32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29	29	29	29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211383

CATALOG NUMBER: LSR4B15D010BZ EC4B10208050 4LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.1	4.3
10°-20°	165.7	12.1
20°-30°	242.1	17.7
30°-40°	276.9	20.3
40°-50°	266.1	19.5
50°-60°	205.5	15.1
60°-70°	114.7	8.4
70°-80°	33.4	2.4
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	466.9	34.2
0°-40°	743.8	54.5
0°-60°	1215.3	89.0
0°-90°	1364.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1364.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	627	
5°	622	59
15°	588	166
25°	526	242
35°	443	277
45°	347	266
55°	230	205
65°	115	115
75°	29	33
85°	1	1
90°	0	



TEST NUMBER: P211383

CATALOG NUMBER: LSR4B15D010BZ EC4B10208050 4LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	626.8
2.5°	626.8
5°	621.5
7.5°	618.8
10°	610.0
12.5°	599.4
15°	587.9
17.5°	576.5
20°	559.7
22.5°	546.4
25°	526.1
27.5°	505.8
30°	485.5
32.5°	465.2
35°	443.2
37.5°	421.1
40°	395.5
42.5°	372.5
45°	346.9
47.5°	317.8
50°	290.4
52.5°	260.4
55°	230.4
57.5°	199.5
60°	170.4
62.5°	141.2
65°	114.8
67.5°	90.0
70°	67.1
72.5°	46.8
75°	29.1
77.5°	15.0
80°	5.3
82.5°	1.8
85°	0.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)