

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211413

Luminaire Tested: **LSR4B15D010BZ EC4B10209050 4LBCSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211413  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B15D010BZ EC4B10209050 4LBCSMW1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM  
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W  
DL3-15.28W DLE-15.432W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1359.2 lumens  
Efficiency: N/A  
Efficacy: 95.0 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211413

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBCSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P211413

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBCSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87																			
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74																			
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63																			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55																			
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48																			
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42																			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37																			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33																			
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30																			
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211413

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBCSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.6	3.9
10°-20°	149.7	11.0
20°-30°	225.2	16.6
30°-40°	267.0	19.6
40°-50°	265.6	19.5
50°-60°	214.2	15.8
60°-70°	129.5	9.5
70°-80°	48.1	3.5
80°-90°	7.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	427.6	31.5
0°-40°	694.5	51.1
0°-60°	1174.3	86.4
0°-90°	1359.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1359.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	555	
5°	553	53
15°	530	150
25°	489	225
35°	428	267
45°	346	266
55°	239	214
65°	130	130
75°	44	48
85°	6	7
90°	0	



TEST NUMBER: P211413

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBCSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	555.1
2.5°	555.1
5°	552.7
7.5°	551.0
10°	546.1
12.5°	537.8
15°	530.4
17.5°	522.2
20°	512.3
22.5°	502.4
25°	489.2
27.5°	475.2
30°	459.6
32.5°	444.8
35°	427.5
37.5°	409.3
40°	387.9
42.5°	367.3
45°	345.9
47.5°	322.0
50°	295.7
52.5°	268.5
55°	238.9
57.5°	212.5
60°	182.8
62.5°	156.5
65°	130.1
67.5°	105.4
70°	82.4
72.5°	61.8
75°	43.7
77.5°	28.0
80°	16.5
82.5°	9.9
85°	5.8
87.5°	2.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)