

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211420

Luminaire Tested: **LSR4B15D010BZ EC4B10209050 4LBNB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211420
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209050 4LBNB1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 505.3 lumens
Efficiency: N/A
Efficacy: 35.3 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211420

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBNB1

Luminous Intensity Polar Plot





TEST NUMBER: P211420

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBNB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88																			
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83																			
4	99	92	86	82	97	90	86	82	88	84	81	86	83	80	85	82	79	78																			
5	94	86	81	77	92	85	80	76	84	79	76	82	78	75	80	77	74	73																			
6	90	81	76	72	88	81	75	71	79	74	71	78	74	70	76	73	70	69																			
7	86	77	71	67	84	76	71	67	75	70	67	74	69	66	73	69	66	65																			
8	82	73	67	63	80	72	67	63	71	66	63	70	66	62	69	65	62	61																			
9	78	69	63	60	77	68	63	59	67	63	59	67	62	59	66	62	59	58																			
10	75	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	54																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211420

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBNB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	13.6
10°-20°	146.0	28.9
20°-30°	169.4	33.5
30°-40°	106.1	21.0
40°-50°	14.9	3.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	384.3	76.0
0°-40°	490.3	97.0
0°-60°	505.3	100.0
0°-90°	505.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	505.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	826	
5°	766	69
15°	519	146
25°	374	169
35°	170	106
45°	13	15
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P211420

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBNB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	826.2
2.5°	809.9
5°	765.6
7.5°	702.0
10°	637.0
12.5°	574.9
15°	518.8
17.5°	471.5
20°	436.0
22.5°	403.5
25°	373.9
27.5°	338.5
30°	292.6
32.5°	235.0
35°	170.0
37.5°	110.8
40°	63.6
42.5°	32.5
45°	13.3
47.5°	3.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)