

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211958

Luminaire Tested: **LE_4B30D010 EC4B30508030 4L1BWH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211958
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508030 4L1BWH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2829.7 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211958

CATALOG NUMBER: LE_4B30D010 EC4B30508030 4L1BWH

Luminous Intensity Polar Plot





TEST NUMBER: P211958

CATALOG NUMBER: LE_4B30D010 EC4B30508030 4L1BWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211958

CATALOG NUMBER: LE_4B30D010 EC4B30508030 4L1BWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.7	6.1
10°-20°	500.5	17.7
20°-30°	738.5	26.1
30°-40°	728.8	25.8
40°-50°	446.0	15.8
50°-60°	171.0	6.0
60°-70°	53.4	1.9
70°-80°	15.7	0.6
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1412.7	49.9
0°-40°	2141.5	75.7
0°-60°	2758.5	97.5
0°-90°	2829.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2829.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1824	
5°	1824	174
15°	1774	500
25°	1617	739
35°	1183	729
45°	572	446
55°	180	171
65°	50	53
75°	15	16
85°	0	2
90°	0	



TEST NUMBER: P211958

CATALOG NUMBER: LE_4B30D010 EC4B30508030 4L1BWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1823.9
2.5°	1827.7
5°	1823.9
7.5°	1820.0
10°	1808.6
12.5°	1793.1
15°	1774.0
17.5°	1750.9
20°	1716.3
22.5°	1677.9
25°	1616.6
27.5°	1539.8
30°	1443.7
32.5°	1324.7
35°	1182.6
37.5°	1025.2
40°	864.0
42.5°	714.2
45°	572.1
47.5°	445.4
50°	337.9
52.5°	249.6
55°	180.5
57.5°	126.7
60°	92.1
62.5°	69.1
65°	49.9
67.5°	38.4
70°	26.9
72.5°	19.3
75°	15.3
77.5°	7.7
80°	7.7
82.5°	3.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)