

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211442

Luminaire Tested: **LSR4B20D010BZ EC4B10209024 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211442
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10209024 4LBCSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1526.7 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211442

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211442

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 110 | 106 | 102 | 99 | 108 | 104 | 100 | 97 | 100 | 97 | 94 | 96 | 93 | 91 | 92 | 90 | 89 | 87 | | | | | | | | | | | | | | | | | | | |
| 2 | 101 | 94 | 87 | 82 | 99 | 92 | 86 | 81 | 88 | 84 | 79 | 85 | 81 | 78 | 82 | 79 | 76 | 74 | | | | | | | | | | | | | | | | | | | |
| 3 | 93 | 83 | 75 | 70 | 90 | 81 | 74 | 69 | 79 | 73 | 68 | 76 | 71 | 67 | 73 | 69 | 65 | 63 | | | | | | | | | | | | | | | | | | | |
| 4 | 85 | 74 | 66 | 60 | 83 | 73 | 65 | 59 | 70 | 64 | 58 | 68 | 62 | 58 | 66 | 61 | 57 | 55 | | | | | | | | | | | | | | | | | | | |
| 5 | 79 | 66 | 58 | 52 | 77 | 65 | 57 | 51 | 63 | 56 | 51 | 61 | 55 | 50 | 60 | 54 | 50 | 48 | | | | | | | | | | | | | | | | | | | |
| 6 | 73 | 60 | 52 | 45 | 71 | 59 | 51 | 45 | 57 | 50 | 45 | 56 | 49 | 44 | 54 | 49 | 44 | 42 | | | | | | | | | | | | | | | | | | | |
| 7 | 68 | 55 | 46 | 40 | 66 | 54 | 46 | 40 | 52 | 45 | 40 | 51 | 44 | 40 | 50 | 44 | 39 | 37 | | | | | | | | | | | | | | | | | | | |
| 8 | 63 | 50 | 42 | 36 | 61 | 49 | 41 | 36 | 48 | 41 | 36 | 47 | 40 | 36 | 46 | 40 | 35 | 33 | | | | | | | | | | | | | | | | | | | |
| 9 | 59 | 46 | 38 | 33 | 57 | 45 | 38 | 32 | 44 | 37 | 32 | 43 | 37 | 32 | 42 | 36 | 32 | 30 | | | | | | | | | | | | | | | | | | | |
| 10 | 55 | 42 | 35 | 30 | 54 | 42 | 34 | 30 | 41 | 34 | 29 | 40 | 34 | 29 | 39 | 33 | 29 | 27 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211442

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBCSMW1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 59.1 | 3.9 |
| 10°-20° | 168.2 | 11.0 |
| 20°-30° | 253.0 | 16.6 |
| 30°-40° | 299.9 | 19.6 |
| 40°-50° | 298.4 | 19.5 |
| 50°-60° | 240.6 | 15.8 |
| 60°-70° | 145.5 | 9.5 |
| 70°-80° | 54.0 | 3.5 |
| 80°-90° | 8.1 | 0.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 480.3 | 31.5 |
| 0°-40° | 780.1 | 51.1 |
| 0°-60° | 1319.1 | 86.4 |
| 0°-90° | 1526.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1526.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 624 | |
| 5° | 621 | 59 |
| 15° | 596 | 168 |
| 25° | 550 | 253 |
| 35° | 480 | 300 |
| 45° | 389 | 298 |
| 55° | 268 | 241 |
| 65° | 146 | 146 |
| 75° | 49 | 54 |
| 85° | 6 | 8 |
| 90° | 0 | |



TEST NUMBER: P211442

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBCSMW1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 623.6 |
| 2.5° | 623.6 |
| 5° | 620.8 |
| 7.5° | 618.9 |
| 10° | 613.4 |
| 12.5° | 604.1 |
| 15° | 595.8 |
| 17.5° | 586.6 |
| 20° | 575.4 |
| 22.5° | 564.3 |
| 25° | 549.5 |
| 27.5° | 533.8 |
| 30° | 516.2 |
| 32.5° | 499.6 |
| 35° | 480.2 |
| 37.5° | 459.8 |
| 40° | 435.7 |
| 42.5° | 412.6 |
| 45° | 388.6 |
| 47.5° | 361.7 |
| 50° | 332.1 |
| 52.5° | 301.6 |
| 55° | 268.3 |
| 57.5° | 238.7 |
| 60° | 205.4 |
| 62.5° | 175.8 |
| 65° | 146.2 |
| 67.5° | 118.4 |
| 70° | 92.5 |
| 72.5° | 69.4 |
| 75° | 49.0 |
| 77.5° | 31.5 |
| 80° | 18.5 |
| 82.5° | 11.1 |
| 85° | 6.5 |
| 87.5° | 2.8 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)