

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211940

Luminaire Tested: **LE_4B30D010 EC4B30508030 4LBM1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211940
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508030 4LBM1MW
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2649.3 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211940

CATALOG NUMBER: LE_4B30D010 EC4B30508030 4LBM1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211940

CATALOG NUMBER: LE_4B30D010 EC4B30508030 4LBM1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89			
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64			
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53			
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49			
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42			
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211940

CATALOG NUMBER: LE_4B30D010 EC4B30508030 4LBM1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	7.0
10°-20°	499.7	18.9
20°-30°	664.5	25.1
30°-40°	543.5	20.5
40°-50°	316.6	11.9
50°-60°	210.0	7.9
60°-70°	138.1	5.2
70°-80°	72.8	2.7
80°-90°	17.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1350.6	51.0
0°-40°	1894.1	71.5
0°-60°	2420.6	91.4
0°-90°	2649.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2649.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2011	
5°	1988	186
15°	1781	500
25°	1458	664
35°	867	543
45°	399	317
55°	234	210
65°	138	138
75°	69	73
85°	15	18
90°	0	



TEST NUMBER: P211940

CATALOG NUMBER: LE_4B30D010 EC4B30508030 4LBM1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2011.1
2.5°	2007.3
5°	1988.1
7.5°	1942.1
10°	1892.2
12.5°	1846.1
15°	1780.8
17.5°	1707.9
20°	1646.5
22.5°	1562.1
25°	1458.5
27.5°	1347.1
30°	1205.1
32.5°	1036.2
35°	867.4
37.5°	713.9
40°	579.5
42.5°	475.9
45°	399.2
47.5°	337.8
50°	295.6
52.5°	261.0
55°	234.1
57.5°	207.3
60°	180.4
62.5°	161.2
65°	138.2
67.5°	119.0
70°	99.8
72.5°	84.4
75°	69.1
77.5°	53.7
80°	38.4
82.5°	26.9
85°	15.3
87.5°	3.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)