

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211455

Luminaire Tested: **LSR4B20D010BZ EC4B10209024 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211455
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10209024 4LBPSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1560.0 lumens
Efficiency: N/A
Efficacy: 75.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211455

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211455

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211455

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.6	3.8
10°-20°	169.8	10.9
20°-30°	255.7	16.4
30°-40°	304.2	19.5
40°-50°	303.7	19.5
50°-60°	246.9	15.8
60°-70°	151.9	9.7
70°-80°	58.9	3.8
80°-90°	9.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	485.0	31.1
0°-40°	789.2	50.6
0°-60°	1339.8	85.9
0°-90°	1560.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1560.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	628	
5°	627	60
15°	603	170
25°	556	256
35°	487	304
45°	395	304
55°	276	247
65°	152	152
75°	54	59
85°	7	9
90°	0	



TEST NUMBER: P211455

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	628.5
2.5°	629.5
5°	626.7
7.5°	623.0
10°	618.4
12.5°	610.0
15°	602.7
17.5°	591.6
20°	579.5
22.5°	568.5
25°	556.4
27.5°	539.8
30°	523.2
32.5°	507.4
35°	487.1
37.5°	464.9
40°	444.6
42.5°	419.6
45°	394.7
47.5°	367.9
50°	339.2
52.5°	309.6
55°	276.4
57.5°	244.0
60°	212.6
62.5°	182.1
65°	152.5
67.5°	124.8
70°	98.9
72.5°	74.9
75°	53.6
77.5°	35.1
80°	21.3
82.5°	12.9
85°	7.4
87.5°	3.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)