

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211961

Luminaire Tested: **LE_4B30D010 EC4B30508030 4LBW1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211961
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508030 4LBW1WH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2937.2 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211961

CATALOG NUMBER: LE_4B30D010 EC4B30508030 4LBW1WH

Luminous Intensity Polar Plot





TEST NUMBER: P211961

CATALOG NUMBER: LE_4B30D010 EC4B30508030 4LBW1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58	58	58	58
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53	53	53	53
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49	49	49	49
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45	45	45	45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211961

CATALOG NUMBER: LE_4B30D010 EC4B30508030 4LBW1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.9	6.1
10°-20°	550.5	18.7
20°-30°	846.8	28.8
30°-40°	817.0	27.8
40°-50°	425.9	14.5
50°-60°	89.7	3.1
60°-70°	20.8	0.7
70°-80°	8.1	0.3
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1575.2	53.6
0°-40°	2392.2	81.4
0°-60°	2907.8	99.0
0°-90°	2937.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2937.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1836	
5°	1852	178
15°	1948	550
25°	1856	847
35°	1326	817
45°	542	426
55°	81	90
65°	19	21
75°	8	8
85°	0	1
90°	0	



TEST NUMBER: P211961

CATALOG NUMBER: LE_4B30D010 EC4B30508030 4LBW1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1836.5
2.5°	1840.3
5°	1851.8
7.5°	1867.3
10°	1890.2
12.5°	1921.0
15°	1947.9
17.5°	1963.3
20°	1951.7
22.5°	1928.7
25°	1855.7
27.5°	1767.4
30°	1652.1
32.5°	1498.4
35°	1325.5
37.5°	1137.3
40°	941.3
42.5°	745.3
45°	541.7
47.5°	364.9
50°	234.3
52.5°	142.1
55°	80.7
57.5°	50.0
60°	34.6
62.5°	26.9
65°	19.3
67.5°	15.3
70°	11.5
72.5°	11.5
75°	7.7
77.5°	3.8
80°	3.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)