

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211456

Luminaire Tested: **LSR4B20D010BZ EC4B10209024 4LBSB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211456  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B20D010BZ EC4B10209024 4LBSB1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1263.0 lumens  
Efficiency: N/A  
Efficacy: 60.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211456

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBSB1

### Luminous Intensity Polar Plot





TEST NUMBER: P211456

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBSB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76			76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65			65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50			50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39			39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			29

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211456

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBSB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.6	4.2
10°-20°	149.2	11.8
20°-30°	221.9	17.6
30°-40°	258.3	20.5
40°-50°	251.8	19.9
50°-60°	193.6	15.3
60°-70°	107.1	8.5
70°-80°	28.3	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	423.8	33.6
0°-40°	682.1	54.0
0°-60°	1127.4	89.3
0°-90°	1263.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1263.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	557	
5°	554	53
15°	528	149
25°	482	222
35°	415	258
45°	327	252
55°	216	194
65°	107	107
75°	24	28
85°	0	0
90°	0	



TEST NUMBER: P211456

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBSB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	557.2
2.5°	557.2
5°	554.0
7.5°	549.2
10°	546.0
12.5°	536.4
15°	528.4
17.5°	520.4
20°	509.1
22.5°	497.9
25°	481.9
27.5°	465.9
30°	449.9
32.5°	432.3
35°	414.7
37.5°	392.3
40°	373.1
42.5°	352.2
45°	326.6
47.5°	302.6
50°	275.4
52.5°	246.6
55°	216.1
57.5°	187.3
60°	160.1
62.5°	132.9
65°	107.3
67.5°	83.3
70°	60.8
72.5°	41.6
75°	24.0
77.5°	11.2
80°	1.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)