

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211964

Luminaire Tested: **LE_4B30D010 EC4B30509030 4LBCS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211964
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509030 4LBCS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3016.6 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211964

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBCS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211964

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBCS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211964

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBCS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.7	3.9
10°-20°	332.3	11.0
20°-30°	499.9	16.6
30°-40°	592.5	19.6
40°-50°	589.6	19.5
50°-60°	475.3	15.8
60°-70°	287.5	9.5
70°-80°	106.8	3.5
80°-90°	15.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	949.0	31.5
0°-40°	1541.5	51.1
0°-60°	2606.4	86.4
0°-90°	3016.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3016.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1232	
5°	1227	117
15°	1177	332
25°	1086	500
35°	949	592
45°	768	590
55°	530	475
65°	289	288
75°	97	107
85°	13	16
90°	0	



TEST NUMBER: P211964

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBCS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1232.0
2.5°	1232.0
5°	1226.6
7.5°	1222.9
10°	1212.0
12.5°	1193.6
15°	1177.2
17.5°	1159.0
20°	1137.0
22.5°	1115.1
25°	1085.9
27.5°	1054.8
30°	1020.0
32.5°	987.2
35°	948.8
37.5°	908.5
40°	861.0
42.5°	815.2
45°	767.8
47.5°	714.8
50°	656.2
52.5°	595.9
55°	530.1
57.5°	471.7
60°	405.8
62.5°	347.3
65°	288.8
67.5°	234.0
70°	182.8
72.5°	137.1
75°	96.9
77.5°	62.2
80°	36.5
82.5°	21.9
85°	12.8
87.5°	5.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)