

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211967

Luminaire Tested: **LE\_4B30D010 EC4B30509030 4LBM1H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211967  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B30D010 EC4B30509030 4LBM1H  
Description: PORTFOLIO 4 INCH CYLINDER  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2173.9 lumens  
Efficiency: N/A  
Efficacy: 77.6 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211967  
CATALOG NUMBER: LE\_4B30D010 EC4B30509030 4LBM1H

### Luminous Intensity Polar Plot





TEST NUMBER: P211967

CATALOG NUMBER: LE\_4B30D010 EC4B30509030 4LBM1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73			73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67			67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			47

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211967

CATALOG NUMBER: LE\_4B30D010 EC4B30509030 4LBM1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	198.4	9.1
10°-20°	520.4	23.9
20°-30°	668.7	30.8
30°-40°	503.2	23.1
40°-50°	202.1	9.3
50°-60°	57.4	2.6
60°-70°	18.2	0.8
70°-80°	5.1	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1387.5	63.8
0°-40°	1890.7	87.0
0°-60°	2150.1	98.9
0°-90°	2173.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2173.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2156	
5°	2116	198
15°	1857	520
25°	1476	669
35°	807	503
45°	249	202
55°	59	57
65°	16	18
75°	3	5
85°	0	0
90°	0	



TEST NUMBER: P211967

CATALOG NUMBER: LE\_4B30D010 EC4B30509030 4LBM1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2155.7
2.5°	2142.5
5°	2116.3
7.5°	2067.1
10°	2004.7
12.5°	1929.3
15°	1857.2
17.5°	1775.0
20°	1686.5
22.5°	1591.3
25°	1476.4
27.5°	1338.6
30°	1177.9
32.5°	997.5
35°	807.1
37.5°	630.0
40°	472.5
42.5°	347.8
45°	249.4
47.5°	170.6
50°	118.1
52.5°	82.0
55°	59.0
57.5°	42.7
60°	32.8
62.5°	23.0
65°	16.4
67.5°	13.1
70°	9.9
72.5°	6.6
75°	3.2
77.5°	3.2
80°	3.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)