

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211461

Luminaire Tested: **LSR4B20D010BZ EC4B10209024 4LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211461
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10209024 4LBSWH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1444.9 lumens
Efficiency: N/A
Efficacy: 69.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211461

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P211461

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77																			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67																			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59																			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211461

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.5	5.5
10°-20°	205.7	14.2
20°-30°	269.1	18.6
30°-40°	284.9	19.7
40°-50°	265.7	18.4
50°-60°	201.3	13.9
60°-70°	109.0	7.5
70°-80°	29.3	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	554.3	38.4
0°-40°	839.2	58.1
0°-60°	1306.2	90.4
0°-90°	1444.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1444.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	862	
5°	849	79
15°	735	206
25°	585	269
35°	455	285
45°	346	266
55°	226	201
65°	109	109
75°	25	29
85°	0	0
90°	0	



TEST NUMBER: P211461

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	861.7
2.5°	858.5
5°	849.1
7.5°	828.5
10°	801.6
12.5°	770.0
15°	735.2
17.5°	695.7
20°	660.9
22.5°	621.4
25°	585.0
27.5°	548.6
30°	513.9
32.5°	483.8
35°	455.4
37.5°	426.9
40°	400.0
42.5°	373.1
45°	346.3
47.5°	316.2
50°	286.2
52.5°	256.1
55°	226.1
57.5°	194.5
60°	164.4
62.5°	136.0
65°	109.1
67.5°	83.8
70°	61.7
72.5°	42.7
75°	25.3
77.5°	11.1
80°	3.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)