

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211970

Luminaire Tested: **LE\_4B30D010 EC4B30509030 4LBM1WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211970  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B30D010 EC4B30509030 4LBM1WH  
Description: PORTFOLIO 4 INCH CYLINDER  
MEDIUM DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2219.9 lumens  
Efficiency: N/A  
Efficacy: 79.3 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211970

CATALOG NUMBER: LE\_4B30D010 EC4B30509030 4LBM1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P211970

CATALOG NUMBER: LE\_4B30D010 EC4B30509030 4LBM1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	105	105	103	101	101	100	98	98	96	95	94			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71			
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66			
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211970

CATALOG NUMBER: LE\_4B30D010 EC4B30509030 4LBM1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	243.6	11.0
10°-20°	626.2	28.2
20°-30°	734.7	33.1
30°-40°	464.9	20.9
40°-50°	124.5	5.6
50°-60°	17.4	0.8
60°-70°	6.5	0.3
70°-80°	2.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1604.4	72.3
0°-40°	2069.4	93.2
0°-60°	2211.3	99.6
0°-90°	2219.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2219.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2636	
5°	2594	244
15°	2243	626
25°	1623	735
35°	738	465
45°	141	125
55°	16	17
65°	7	6
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P211970

CATALOG NUMBER: LE\_4B30D010 EC4B30509030 4LBM1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2636.4
2.5°	2626.6
5°	2593.9
7.5°	2541.3
10°	2465.9
12.5°	2367.6
15°	2243.0
17.5°	2115.0
20°	1961.0
22.5°	1803.6
25°	1623.2
27.5°	1426.5
30°	1206.7
32.5°	967.3
35°	737.8
37.5°	534.5
40°	367.3
42.5°	236.1
45°	141.1
47.5°	78.6
50°	42.6
52.5°	23.0
55°	16.4
57.5°	13.1
60°	9.9
62.5°	9.9
65°	6.6
67.5°	3.2
70°	3.2
72.5°	3.2
75°	3.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)