

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211468

Luminaire Tested: **LSR4B20D010BZ EC4B10209024 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211468
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10209024 4LBWWH1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1269.5 lumens
Efficiency: N/A
Efficacy: 61.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211468

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P211468

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84			84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63			63
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58			58
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53			53
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49			49
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45			45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41			41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211468

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.9	6.1
10°-20°	237.9	18.7
20°-30°	366.0	28.8
30°-40°	353.1	27.8
40°-50°	184.1	14.5
50°-60°	38.8	3.1
60°-70°	9.0	0.7
70°-80°	3.5	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	680.8	53.6
0°-40°	1033.9	81.4
0°-60°	1256.8	99.0
0°-90°	1269.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1269.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	794	
5°	800	77
15°	842	238
25°	802	366
35°	573	353
45°	234	184
55°	35	39
65°	8	9
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P211468

CATALOG NUMBER: LSR4B20D010BZ EC4B10209024 4LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	793.8
2.5°	795.4
5°	800.4
7.5°	807.1
10°	817.0
12.5°	830.3
15°	841.9
17.5°	848.6
20°	843.6
22.5°	833.6
25°	802.1
27.5°	763.9
30°	714.1
32.5°	647.6
35°	572.9
37.5°	491.5
40°	406.9
42.5°	322.2
45°	234.1
47.5°	157.8
50°	101.3
52.5°	61.4
55°	34.9
57.5°	21.6
60°	14.9
62.5°	11.6
65°	8.3
67.5°	6.6
70°	5.0
72.5°	5.0
75°	3.3
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)