

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211983

Luminaire Tested: **LE_4B30D010 EC4B30509030 4LBS1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211983
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509030 4LBS1WH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2854.8 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211983

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBS1WH

Luminous Intensity Polar Plot





TEST NUMBER: P211983

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBS1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211983

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBS1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.0	5.5
10°-20°	406.5	14.2
20°-30°	531.6	18.6
30°-40°	562.9	19.7
40°-50°	525.1	18.4
50°-60°	397.7	13.9
60°-70°	215.4	7.5
70°-80°	57.8	2.0
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1095.1	38.4
0°-40°	1658.1	58.1
0°-60°	2580.8	90.4
0°-90°	2854.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2854.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1703	
5°	1678	157
15°	1453	406
25°	1156	532
35°	900	563
45°	684	525
55°	447	398
65°	216	215
75°	50	58
85°	0	1
90°	0	



TEST NUMBER: P211983

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBS1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1702.6
2.5°	1696.4
5°	1677.6
7.5°	1637.0
10°	1583.9
12.5°	1521.5
15°	1452.7
17.5°	1374.6
20°	1305.8
22.5°	1227.7
25°	1155.9
27.5°	1084.0
30°	1015.3
32.5°	956.0
35°	899.7
37.5°	843.4
40°	790.4
42.5°	737.3
45°	684.2
47.5°	624.8
50°	565.5
52.5°	506.1
55°	446.7
57.5°	384.3
60°	324.9
62.5°	268.7
65°	215.5
67.5°	165.5
70°	121.8
72.5°	84.3
75°	50.0
77.5°	21.9
80°	6.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)