

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211985

Luminaire Tested: **LE\_4B30D010 EC4B30509030 4LBW1B**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211985  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B30D010 EC4B30509030 4LBW1B  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1413.3 lumens  
Efficiency: N/A  
Efficacy: 50.5 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211985  
CATALOG NUMBER: LE\_4B30D010 EC4B30509030 4LBW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P211985

CATALOG NUMBER: LE\_4B30D010 EC4B30509030 4LBW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93															
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86				86															
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79				79															
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72				72															
5	90	81	75	70	89	80	74	70	79	73	69	77	72	69	75	71	68	67				67															
6	85	76	69	65	84	75	69	64	73	68	64	72	67	64	70	66	63	62				62															
7	80	71	64	60	79	70	64	59	69	63	59	67	62	59	66	62	58	57				57															
8	76	66	60	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53				53															
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49															
10	68	58	52	48	67	58	52	48	57	51	47	56	51	47	55	50	47	46				46															

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211985

CATALOG NUMBER: LE\_4B30D010 EC4B30509030 4LBW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.4	7.9
10°-20°	315.6	22.3
20°-30°	436.2	30.9
30°-40°	373.5	26.4
40°-50°	158.8	11.2
50°-60°	17.8	1.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	863.2	61.1
0°-40°	1236.7	87.5
0°-60°	1413.3	100.0
0°-90°	1413.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1413.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1180	
5°	1173	111
15°	1121	316
25°	957	436
35°	606	373
45°	200	159
55°	10	18
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P211985

CATALOG NUMBER: LE\_4B30D010 EC4B30509030 4LBW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1179.7
2.5°	1176.5
5°	1173.1
7.5°	1166.6
10°	1153.5
12.5°	1146.9
15°	1120.7
17.5°	1097.8
20°	1061.7
22.5°	1019.2
25°	956.9
27.5°	888.1
30°	809.4
32.5°	714.3
35°	606.2
37.5°	494.9
40°	383.4
42.5°	285.1
45°	199.9
47.5°	124.5
50°	72.0
52.5°	36.1
55°	9.9
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)