

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212019

Luminaire Tested: **LE_4B30D010 EC4B30509730 4LBW1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212019
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509730 4LBW1WH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2192.7 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212019

CATALOG NUMBER: LE_4B30D010 EC4B30509730 4LBW1WH

Luminous Intensity Polar Plot





TEST NUMBER: P212019

CATALOG NUMBER: LE_4B30D010 EC4B30509730 4LBW1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 110 | 107 | 104 | 110 | 107 | 105 | 103 | 103 | 101 | 100 | 100 | 98 | 97 | 96 | 95 | 94 | 92 | | | |
| 2 | 106 | 101 | 96 | 92 | 104 | 99 | 95 | 91 | 96 | 92 | 89 | 93 | 90 | 87 | 90 | 87 | 85 | 84 | | | |
| 3 | 100 | 93 | 87 | 82 | 98 | 91 | 86 | 82 | 88 | 84 | 80 | 86 | 82 | 79 | 84 | 80 | 78 | 76 | | | |
| 4 | 94 | 85 | 79 | 74 | 92 | 84 | 78 | 74 | 82 | 77 | 73 | 80 | 75 | 72 | 78 | 74 | 71 | 69 | | | |
| 5 | 88 | 79 | 72 | 67 | 86 | 78 | 71 | 67 | 76 | 70 | 66 | 74 | 69 | 65 | 72 | 68 | 65 | 63 | | | |
| 6 | 83 | 73 | 66 | 61 | 81 | 72 | 65 | 61 | 70 | 64 | 60 | 69 | 64 | 60 | 67 | 63 | 59 | 58 | | | |
| 7 | 78 | 67 | 60 | 56 | 76 | 67 | 60 | 55 | 65 | 59 | 55 | 64 | 59 | 55 | 63 | 58 | 54 | 53 | | | |
| 8 | 73 | 62 | 56 | 51 | 72 | 62 | 55 | 51 | 61 | 55 | 51 | 60 | 54 | 50 | 59 | 54 | 50 | 49 | | | |
| 9 | 69 | 58 | 51 | 47 | 68 | 58 | 51 | 47 | 57 | 51 | 47 | 56 | 50 | 47 | 55 | 50 | 46 | 45 | | | |
| 10 | 65 | 54 | 48 | 43 | 64 | 54 | 48 | 43 | 53 | 47 | 43 | 52 | 47 | 43 | 51 | 46 | 43 | 41 | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212019

CATALOG NUMBER: LE_4B30D010 EC4B30509730 4LBW1WH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 132.8 | 6.1 |
| 10°-20° | 410.9 | 18.7 |
| 20°-30° | 632.1 | 28.8 |
| 30°-40° | 609.9 | 27.8 |
| 40°-50° | 318.0 | 14.5 |
| 50°-60° | 66.9 | 3.1 |
| 60°-70° | 15.6 | 0.7 |
| 70°-80° | 6.0 | 0.3 |
| 80°-90° | 0.4 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1175.9 | 53.6 |
| 0°-40° | 1785.8 | 81.4 |
| 0°-60° | 2170.7 | 99.0 |
| 0°-90° | 2192.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2192.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1371 | |
| 5° | 1382 | 133 |
| 15° | 1454 | 411 |
| 25° | 1385 | 632 |
| 35° | 990 | 610 |
| 45° | 404 | 318 |
| 55° | 60 | 67 |
| 65° | 14 | 16 |
| 75° | 6 | 6 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P212019

CATALOG NUMBER: LE_4B30D010 EC4B30509730 4LBW1WH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1370.9 |
| 2.5° | 1373.8 |
| 5° | 1382.4 |
| 7.5° | 1393.9 |
| 10° | 1411.1 |
| 12.5° | 1434.0 |
| 15° | 1454.1 |
| 17.5° | 1465.5 |
| 20° | 1457.0 |
| 22.5° | 1439.8 |
| 25° | 1385.3 |
| 27.5° | 1319.3 |
| 30° | 1233.3 |
| 32.5° | 1118.6 |
| 35° | 989.5 |
| 37.5° | 849.0 |
| 40° | 702.7 |
| 42.5° | 556.5 |
| 45° | 404.4 |
| 47.5° | 272.5 |
| 50° | 174.9 |
| 52.5° | 106.1 |
| 55° | 60.2 |
| 57.5° | 37.2 |
| 60° | 25.9 |
| 62.5° | 20.1 |
| 65° | 14.4 |
| 67.5° | 11.5 |
| 70° | 8.6 |
| 72.5° | 8.6 |
| 75° | 5.7 |
| 77.5° | 2.9 |
| 80° | 2.9 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)