

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212045

Luminaire Tested: **LE_4B30D010 EC4B30508035 4L1BWH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212045
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508035 4L1BWH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2899.8 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212045

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4L1BWH

Luminous Intensity Polar Plot





TEST NUMBER: P212045

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4L1BWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55		
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50		
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46		
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43		
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212045

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4L1BWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.0	6.1
10°-20°	512.9	17.7
20°-30°	756.8	26.1
30°-40°	746.9	25.8
40°-50°	457.1	15.8
50°-60°	175.2	6.0
60°-70°	54.8	1.9
70°-80°	16.1	0.6
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1447.7	49.9
0°-40°	2194.6	75.7
0°-60°	2826.8	97.5
0°-90°	2899.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2899.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1869	
5°	1869	178
15°	1818	513
25°	1657	757
35°	1212	747
45°	586	457
55°	185	175
65°	51	55
75°	16	16
85°	0	2
90°	0	



TEST NUMBER: P212045

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4L1BWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1869.1
2.5°	1873.1
5°	1869.1
7.5°	1865.2
10°	1853.3
12.5°	1837.6
15°	1818.0
17.5°	1794.3
20°	1758.9
22.5°	1719.6
25°	1656.6
27.5°	1577.8
30°	1479.5
32.5°	1357.5
35°	1212.0
37.5°	1050.6
40°	885.3
42.5°	731.8
45°	586.3
47.5°	456.5
50°	346.3
52.5°	255.8
55°	184.9
57.5°	129.8
60°	94.4
62.5°	70.9
65°	51.2
67.5°	39.3
70°	27.5
72.5°	19.7
75°	15.8
77.5°	7.9
80°	7.9
82.5°	3.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)