

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211490

Luminaire Tested: **LSR4B20D010BZ EC4B10208027 4LBSWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211490  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B20D010BZ EC4B10208027 4LBSWH1  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1913.4 lumens  
Efficiency: N/A  
Efficacy: 92.0 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211490

CATALOG NUMBER: LSR4B20D010BZ EC4B10208027 4LBSWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P211490

CATALOG NUMBER: LSR4B20D010BZ EC4B10208027 4LBSWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77																			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67																			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59																			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211490

CATALOG NUMBER: LSR4B20D010BZ EC4B10208027 4LBSWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.2	5.5
10°-20°	272.4	14.2
20°-30°	356.3	18.6
30°-40°	377.3	19.7
40°-50°	351.9	18.4
50°-60°	266.5	13.9
60°-70°	144.4	7.5
70°-80°	38.7	2.0
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	734.0	38.4
0°-40°	1111.3	58.1
0°-60°	1729.7	90.4
0°-90°	1913.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1913.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1141	
5°	1124	105
15°	974	272
25°	775	356
35°	603	377
45°	458	352
55°	299	267
65°	144	144
75°	34	39
85°	0	1
90°	0	



TEST NUMBER: P211490

CATALOG NUMBER: LSR4B20D010BZ EC4B10208027 4LBSWH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1141.1
2.5°	1136.9
5°	1124.4
7.5°	1097.2
10°	1061.6
12.5°	1019.7
15°	973.6
17.5°	921.3
20°	875.2
22.5°	822.9
25°	774.7
27.5°	726.5
30°	680.5
32.5°	640.7
35°	603.0
37.5°	565.3
40°	529.7
42.5°	494.1
45°	458.5
47.5°	418.8
50°	379.0
52.5°	339.2
55°	299.4
57.5°	257.5
60°	217.8
62.5°	180.1
65°	144.5
67.5°	111.0
70°	81.7
72.5°	56.5
75°	33.5
77.5°	14.7
80°	4.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)