

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212025

Luminaire Tested: **LE_4B30D010 EC4B30508035 4LBM1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212025
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508035 4LBM1H
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2608.7 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212025

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBM1H

Luminous Intensity Polar Plot





TEST NUMBER: P212025

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBM1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73			73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67			67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212025

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBM1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.0	9.1
10°-20°	624.4	23.9
20°-30°	802.5	30.8
30°-40°	603.8	23.1
40°-50°	242.5	9.3
50°-60°	68.9	2.6
60°-70°	21.8	0.8
70°-80°	6.2	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1664.9	63.8
0°-40°	2268.7	87.0
0°-60°	2580.1	98.9
0°-90°	2608.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2608.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2587	
5°	2540	238
15°	2228	624
25°	1772	802
35°	968	604
45°	299	242
55°	71	69
65°	20	22
75°	4	6
85°	0	1
90°	0	



TEST NUMBER: P212025

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBM1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2586.7
2.5°	2570.9
5°	2539.5
7.5°	2480.4
10°	2405.6
12.5°	2315.0
15°	2228.4
17.5°	2130.0
20°	2023.6
22.5°	1909.5
25°	1771.7
27.5°	1606.4
30°	1413.5
32.5°	1196.9
35°	968.5
37.5°	756.0
40°	566.9
42.5°	417.4
45°	299.2
47.5°	204.7
50°	141.8
52.5°	98.5
55°	70.9
57.5°	51.2
60°	39.3
62.5°	27.6
65°	19.7
67.5°	15.8
70°	11.8
72.5°	7.9
75°	3.9
77.5°	3.9
80°	3.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)