

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212036

Luminaire Tested: **LE_4B30D010 EC4B30508035 4LBS1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212036
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508035 4LBS1B
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2994.7 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212036

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P212036

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88			
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76			
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65			
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50			
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39			
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212036

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.7	4.2
10°-20°	353.8	11.8
20°-30°	526.2	17.6
30°-40°	612.4	20.4
40°-50°	596.9	19.9
50°-60°	459.1	15.3
60°-70°	253.8	8.5
70°-80°	67.2	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1004.7	33.5
0°-40°	1617.1	54.0
0°-60°	2673.1	89.3
0°-90°	2994.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2994.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1321	
5°	1314	125
15°	1253	354
25°	1143	526
35°	983	612
45°	774	597
55°	512	459
65°	254	254
75°	57	67
85°	0	1
90°	0	



TEST NUMBER: P212036

CATALOG NUMBER: LE_4B30D010 EC4B30508035 4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1321.0
2.5°	1321.0
5°	1313.5
7.5°	1302.0
10°	1294.4
12.5°	1271.7
15°	1252.7
17.5°	1233.7
20°	1207.1
22.5°	1180.5
25°	1142.6
27.5°	1104.7
30°	1066.7
32.5°	1025.0
35°	983.2
37.5°	930.0
40°	884.5
42.5°	835.1
45°	774.4
47.5°	717.5
50°	653.0
52.5°	584.6
55°	512.5
57.5°	444.2
60°	379.6
62.5°	315.1
65°	254.4
67.5°	197.4
70°	144.3
72.5°	98.7
75°	57.0
77.5°	26.6
80°	3.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)