

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212079

Luminaire Tested: **LE\_4B30D010 EC4B30508040 4LBCS1MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P212079  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B30D010 EC4B30508040 4LBCS1MMS  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3091.4 lumens  
Efficiency: N/A  
Efficacy: 110.4 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P212079

CATALOG NUMBER: LE\_4B30D010 EC4B30508040 4LBCS1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P212079

CATALOG NUMBER: LE\_4B30D010 EC4B30508040 4LBCS1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88																
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	83	80	78	76			76																
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65																
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57																
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50																
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44																
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40																
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36																
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32																
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29																

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P212079

CATALOG NUMBER: LE\_4B30D010 EC4B30508040 4LBCS1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	133.8	4.3
10°-20°	375.4	12.1
20°-30°	548.3	17.7
30°-40°	627.1	20.3
40°-50°	602.7	19.5
50°-60°	465.4	15.1
60°-70°	259.8	8.4
70°-80°	75.6	2.4
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1057.5	34.2
0°-40°	1684.7	54.5
0°-60°	2752.8	89.0
0°-90°	3091.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3091.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1420	
5°	1408	134
15°	1332	375
25°	1192	548
35°	1004	627
45°	786	603
55°	522	465
65°	260	260
75°	66	76
85°	2	3
90°	0	



TEST NUMBER: P212079

CATALOG NUMBER: LE\_4B30D010 EC4B30508040 4LBCS1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1419.7
2.5°	1419.7
5°	1407.7
7.5°	1401.6
10°	1381.7
12.5°	1357.7
15°	1331.7
17.5°	1305.7
20°	1267.8
22.5°	1237.7
25°	1191.8
27.5°	1145.7
30°	1099.8
32.5°	1053.7
35°	1003.7
37.5°	953.8
40°	895.8
42.5°	843.8
45°	785.8
47.5°	719.8
50°	657.8
52.5°	589.9
55°	521.9
57.5°	451.9
60°	385.9
62.5°	319.9
65°	260.0
67.5°	203.9
70°	152.0
72.5°	106.0
75°	66.0
77.5°	34.0
80°	11.9
82.5°	3.9
85°	2.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)