

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211533

Luminaire Tested: **LSR4B20D010BZ EC4B10209727 4LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211533
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10209727 4LBML1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1356.7 lumens
Efficiency: N/A
Efficacy: 65.2 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211533

CATALOG NUMBER: LSR4B20D010BZ EC4B10209727 4LBML11

Luminous Intensity Polar Plot





TEST NUMBER: P211533

CATALOG NUMBER: LSR4B20D010BZ EC4B10209727 4LBML11

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																																				
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88																																				
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83																																				
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78																																				
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73																																				
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69																																				
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65																																				
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62																																				
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58																																				
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211533

CATALOG NUMBER: LSR4B20D010BZ EC4B10209727 4LBML11

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.7	14.3
10°-20°	433.0	31.9
20°-30°	430.5	31.7
30°-40°	234.4	17.3
40°-50°	54.2	4.0
50°-60°	7.6	0.6
60°-70°	2.8	0.2
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1057.1	77.9
0°-40°	1291.5	95.2
0°-60°	1353.3	99.7
0°-90°	1356.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1356.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2139	
5°	2095	194
15°	1563	433
25°	944	430
35°	363	234
45°	62	54
55°	8	8
65°	3	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P211533

CATALOG NUMBER: LSR4B20D010BZ EC4B10209727 4LBMLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2138.9
2.5°	2134.0
5°	2094.6
7.5°	2014.1
10°	1902.5
12.5°	1738.4
15°	1562.7
17.5°	1388.7
20°	1218.0
22.5°	1078.5
25°	943.9
27.5°	815.8
30°	671.4
32.5°	510.5
35°	362.8
37.5°	244.6
40°	159.2
42.5°	100.1
45°	62.4
47.5°	36.1
50°	18.1
52.5°	9.8
55°	8.2
57.5°	4.9
60°	4.9
62.5°	3.3
65°	3.3
67.5°	1.6
70°	1.6
72.5°	1.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)