

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212106

Luminaire Tested: **LE_4B30D010 EC4B30508040 4LBW1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212106
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508040 4LBW1WH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3042.4 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212106

CATALOG NUMBER: LE_4B30D010 EC4B30508040 4LBW1WH

Luminous Intensity Polar Plot





TEST NUMBER: P212106

CATALOG NUMBER: LE_4B30D010 EC4B30508040 4LBW1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84			84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63			63
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58			58
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53			53
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49			49
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45			45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41			41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212106

CATALOG NUMBER: LE_4B30D010 EC4B30508040 4LBW1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.3	6.1
10°-20°	570.2	18.7
20°-30°	877.1	28.8
30°-40°	846.3	27.8
40°-50°	441.2	14.5
50°-60°	92.9	3.1
60°-70°	21.6	0.7
70°-80°	8.3	0.3
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1631.6	53.6
0°-40°	2477.9	81.4
0°-60°	3011.9	99.0
0°-90°	3042.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3042.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1902	
5°	1918	184
15°	2018	570
25°	1922	877
35°	1373	846
45°	561	441
55°	84	93
65°	20	22
75°	8	8
85°	0	1
90°	0	



TEST NUMBER: P212106

CATALOG NUMBER: LE_4B30D010 EC4B30508040 4LBW1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1902.3
2.5°	1906.2
5°	1918.2
7.5°	1934.2
10°	1958.0
12.5°	1989.9
15°	2017.7
17.5°	2033.6
20°	2021.6
22.5°	1997.9
25°	1922.2
27.5°	1830.7
30°	1711.2
32.5°	1552.1
35°	1373.0
37.5°	1178.0
40°	975.0
42.5°	772.1
45°	561.1
47.5°	378.0
50°	242.8
52.5°	147.2
55°	83.5
57.5°	51.7
60°	35.8
62.5°	27.8
65°	20.0
67.5°	15.9
70°	11.9
72.5°	11.9
75°	8.0
77.5°	3.9
80°	3.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)