

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211558

Luminaire Tested: **LSR4B20D010BZ EC4B10208030 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211558
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10208030 4LBCSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2113.2 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211558

CATALOG NUMBER: LSR4B20D010BZ EC4B10208030 4LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211558

CATALOG NUMBER: LSR4B20D010BZ EC4B10208030 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0							
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87																			
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74																			
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63																			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55																			
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48																			
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42																			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37																			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33																			
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30																			
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211558

CATALOG NUMBER: LSR4B20D010BZ EC4B10208030 4LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.8	3.9
10°-20°	232.8	11.0
20°-30°	350.2	16.6
30°-40°	415.0	19.6
40°-50°	413.0	19.5
50°-60°	333.0	15.8
60°-70°	201.4	9.5
70°-80°	74.8	3.5
80°-90°	11.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	664.8	31.5
0°-40°	1079.8	51.1
0°-60°	1825.8	86.4
0°-90°	2113.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2113.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	863	
5°	859	82
15°	825	233
25°	761	350
35°	665	415
45°	538	413
55°	371	333
65°	202	201
75°	68	75
85°	9	11
90°	0	



TEST NUMBER: P211558

CATALOG NUMBER: LSR4B20D010BZ EC4B10208030 4LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	863.1
2.5°	863.1
5°	859.2
7.5°	856.7
10°	849.0
12.5°	836.2
15°	824.7
17.5°	811.9
20°	796.5
22.5°	781.1
25°	760.6
27.5°	738.9
30°	714.5
32.5°	691.5
35°	664.6
37.5°	636.4
40°	603.1
42.5°	571.1
45°	537.8
47.5°	500.7
50°	459.7
52.5°	417.5
55°	371.4
57.5°	330.4
60°	284.3
62.5°	243.3
65°	202.3
67.5°	163.9
70°	128.1
72.5°	96.0
75°	67.9
77.5°	43.5
80°	25.6
82.5°	15.4
85°	9.0
87.5°	3.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)