

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211564

Luminaire Tested: **LSR4B20D010BZ EC4B10208030 4LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211564
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B20D010BZ EC4B10208030 4LBMWH1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1555.1 lumens
Efficiency: N/A
Efficacy: 74.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211564

CATALOG NUMBER: LSR4B20D010BZ EC4B10208030 4LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P211564

CATALOG NUMBER: LSR4B20D010BZ EC4B10208030 4LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																			
	1	114	111	108	106	111	109	106	105	105	103	101	101	100	98	98	96	95	94																																			
	2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87																																			
	3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81																																			
	4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76																																			
	5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71																																			
	6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66																																			
	7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62																																			
	8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58																																			
	9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55																																			
	10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52																																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211564

CATALOG NUMBER: LSR4B20D010BZ EC4B10208030 4LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.6	11.0
10°-20°	438.7	28.2
20°-30°	514.6	33.1
30°-40°	325.7	20.9
40°-50°	87.2	5.6
50°-60°	12.2	0.8
60°-70°	4.5	0.3
70°-80°	1.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1123.9	72.3
0°-40°	1449.6	93.2
0°-60°	1549.0	99.6
0°-90°	1555.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1555.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1847	
5°	1817	171
15°	1571	439
25°	1137	515
35°	517	326
45°	99	87
55°	12	12
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P211564

CATALOG NUMBER: LSR4B20D010BZ EC4B10208030 4LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1846.9
2.5°	1840.0
5°	1817.0
7.5°	1780.3
10°	1727.4
12.5°	1658.5
15°	1571.2
17.5°	1481.6
20°	1373.7
22.5°	1263.4
25°	1137.1
27.5°	999.2
30°	845.3
32.5°	677.6
35°	516.8
37.5°	374.4
40°	257.3
42.5°	165.4
45°	98.8
47.5°	55.1
50°	29.9
52.5°	16.1
55°	11.5
57.5°	9.2
60°	6.9
62.5°	6.9
65°	4.6
67.5°	2.3
70°	2.3
72.5°	2.3
75°	2.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)