

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212114

Luminaire Tested: **LE_4B30D010 EC4B30509040 4LBM1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212114
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509040 4LBM1MW
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2298.8 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212114

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBM1MW

Luminous Intensity Polar Plot





TEST NUMBER: P212114

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBM1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 100 | 102 | 99 | 97 | 98 | 96 | 94 | 94 | 93 | 91 | 89 | | | |
| 2 | 104 | 98 | 92 | 88 | 102 | 96 | 91 | 87 | 93 | 89 | 85 | 89 | 86 | 83 | 87 | 84 | 81 | 80 | | | |
| 3 | 97 | 89 | 83 | 77 | 95 | 87 | 82 | 77 | 85 | 80 | 76 | 82 | 78 | 74 | 80 | 76 | 73 | 71 | | | |
| 4 | 91 | 81 | 74 | 69 | 89 | 80 | 74 | 69 | 78 | 72 | 68 | 76 | 71 | 67 | 74 | 69 | 66 | 64 | | | |
| 5 | 85 | 75 | 67 | 62 | 83 | 74 | 67 | 62 | 72 | 66 | 61 | 70 | 65 | 61 | 68 | 64 | 60 | 58 | | | |
| 6 | 80 | 69 | 62 | 56 | 78 | 68 | 61 | 56 | 66 | 60 | 56 | 65 | 59 | 55 | 63 | 59 | 55 | 53 | | | |
| 7 | 75 | 64 | 57 | 52 | 74 | 63 | 56 | 51 | 62 | 56 | 51 | 60 | 55 | 51 | 59 | 54 | 50 | 49 | | | |
| 8 | 71 | 59 | 52 | 47 | 69 | 59 | 52 | 47 | 58 | 51 | 47 | 56 | 51 | 47 | 55 | 50 | 47 | 45 | | | |
| 9 | 67 | 55 | 48 | 44 | 66 | 55 | 48 | 44 | 54 | 48 | 44 | 53 | 47 | 43 | 52 | 47 | 43 | 42 | | | |
| 10 | 63 | 52 | 45 | 41 | 62 | 51 | 45 | 41 | 51 | 45 | 40 | 50 | 44 | 40 | 49 | 44 | 40 | 39 | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212114

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBM1MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 161.8 | 7.0 |
| 10°-20° | 433.6 | 18.9 |
| 20°-30° | 576.6 | 25.1 |
| 30°-40° | 471.6 | 20.5 |
| 40°-50° | 274.7 | 11.9 |
| 50°-60° | 182.1 | 7.9 |
| 60°-70° | 119.8 | 5.2 |
| 70°-80° | 63.2 | 2.7 |
| 80°-90° | 15.4 | 0.7 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1172.0 | 51.0 |
| 0°-40° | 1643.5 | 71.5 |
| 0°-60° | 2100.4 | 91.4 |
| 0°-90° | 2298.8 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2298.8 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1745 | |
| 5° | 1725 | 162 |
| 15° | 1545 | 434 |
| 25° | 1266 | 577 |
| 35° | 753 | 472 |
| 45° | 346 | 275 |
| 55° | 203 | 182 |
| 65° | 120 | 120 |
| 75° | 60 | 63 |
| 85° | 13 | 15 |
| 90° | 0 | |



TEST NUMBER: P212114

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBM1MW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1745.1 |
| 2.5° | 1741.7 |
| 5° | 1725.2 |
| 7.5° | 1685.1 |
| 10° | 1641.9 |
| 12.5° | 1601.8 |
| 15° | 1545.2 |
| 17.5° | 1482.0 |
| 20° | 1428.7 |
| 22.5° | 1355.5 |
| 25° | 1265.6 |
| 27.5° | 1168.9 |
| 30° | 1045.7 |
| 32.5° | 899.2 |
| 35° | 752.6 |
| 37.5° | 619.4 |
| 40° | 502.9 |
| 42.5° | 413.0 |
| 45° | 346.4 |
| 47.5° | 293.0 |
| 50° | 256.5 |
| 52.5° | 226.4 |
| 55° | 203.1 |
| 57.5° | 179.8 |
| 60° | 156.5 |
| 62.5° | 139.9 |
| 65° | 119.9 |
| 67.5° | 103.2 |
| 70° | 86.5 |
| 72.5° | 73.3 |
| 75° | 60.0 |
| 77.5° | 46.6 |
| 80° | 33.3 |
| 82.5° | 23.3 |
| 85° | 13.3 |
| 87.5° | 3.4 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)