

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211584

Luminaire Tested: **LSR4B20D010BZ EC4B10208030 4LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211584  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B20D010BZ EC4B10208030 4LBWWH1  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1757.2 lumens  
Efficiency: N/A  
Efficacy: 84.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211584

CATALOG NUMBER: LSR4B20D010BZ EC4B10208030 4LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P211584

CATALOG NUMBER: LSR4B20D010BZ EC4B10208030 4LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92																			
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84																			
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76																			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69																			
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63																			
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58																			
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53																			
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49																			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45																			
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211584

CATALOG NUMBER: LSR4B20D010BZ EC4B10208030 4LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.5	6.1
10°-20°	329.3	18.7
20°-30°	506.6	28.8
30°-40°	488.8	27.8
40°-50°	254.8	14.5
50°-60°	53.6	3.1
60°-70°	12.5	0.7
70°-80°	4.8	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	942.3	53.6
0°-40°	1431.1	81.4
0°-60°	1739.6	99.0
0°-90°	1757.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1757.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1099	
5°	1108	106
15°	1165	329
25°	1110	507
35°	793	489
45°	324	255
55°	48	54
65°	12	12
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P211584

CATALOG NUMBER: LSR4B20D010BZ EC4B10208030 4LBWWH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1098.7
2.5°	1101.0
5°	1107.9
7.5°	1117.1
10°	1130.9
12.5°	1149.3
15°	1165.3
17.5°	1174.5
20°	1167.6
22.5°	1153.8
25°	1110.2
27.5°	1057.3
30°	988.4
32.5°	896.4
35°	793.0
37.5°	680.4
40°	563.1
42.5°	445.9
45°	324.1
47.5°	218.4
50°	140.2
52.5°	85.0
55°	48.3
57.5°	29.9
60°	20.7
62.5°	16.1
65°	11.5
67.5°	9.2
70°	6.9
72.5°	6.9
75°	4.6
77.5°	2.3
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)