

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212116

Luminaire Tested: **LE_4B30D010 EC4B30509040 4LBN1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212116
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509040 4LBN1B
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1139.4 lumens
Efficiency: N/A
Efficacy: 40.7 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212116

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBN1B

Luminous Intensity Polar Plot





TEST NUMBER: P212116

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBN1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88		
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83		
4	99	92	86	82	97	90	86	82	88	84	81	86	83	80	85	82	79	78		
5	94	86	81	77	92	85	80	76	84	79	76	82	78	75	80	77	74	73		
6	90	81	76	72	88	81	75	71	79	74	71	78	74	70	76	73	70	69		
7	86	77	71	67	84	76	71	67	75	70	67	74	69	66	73	69	66	65		
8	82	73	67	63	80	72	67	63	71	66	63	70	66	62	69	65	62	61		
9	78	69	63	60	77	68	63	59	67	63	59	67	62	59	66	62	59	58		
10	75	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	54		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212116

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBN1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.2	13.6
10°-20°	329.2	28.9
20°-30°	382.0	33.5
30°-40°	239.2	21.0
40°-50°	33.7	3.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	866.5	76.1
0°-40°	1105.7	97.0
0°-60°	1139.4	100.0
0°-90°	1139.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1139.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1863	
5°	1726	155
15°	1170	329
25°	843	382
35°	383	239
45°	30	34
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P212116

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBN1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1863.1
2.5°	1826.4
5°	1726.4
7.5°	1583.2
10°	1436.4
12.5°	1296.5
15°	1169.9
17.5°	1063.1
20°	983.2
22.5°	909.9
25°	843.2
27.5°	763.3
30°	659.9
32.5°	529.9
35°	383.3
37.5°	250.0
40°	143.3
42.5°	73.3
45°	30.0
47.5°	6.6
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)