

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211590

Luminaire Tested: **LSR4B20D010BZ EC4B10209030 4LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211590  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B20D010BZ EC4B10209030 4LBMH1  
Description: PORTFOLIO 4 INCH CYLINDER  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1300.8 lumens  
Efficiency: N/A  
Efficacy: 62.5 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct

Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211590  
CATALOG NUMBER: LSR4B20D010BZ EC4B10209030 4LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P211590

CATALOG NUMBER: LSR4B20D010BZ EC4B10209030 4LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																												
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85																												
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79																												
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73																												
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67																												
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62																												
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58																												
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54																												
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50																												
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47																												

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211590

CATALOG NUMBER: LSR4B20D010BZ EC4B10209030 4LBMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.7	9.1
10°-20°	311.4	23.9
20°-30°	400.2	30.8
30°-40°	301.1	23.1
40°-50°	120.9	9.3
50°-60°	34.3	2.6
60°-70°	10.9	0.8
70°-80°	3.1	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	830.2	63.8
0°-40°	1131.3	87.0
0°-60°	1286.5	98.9
0°-90°	1300.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1300.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1290	
5°	1266	119
15°	1111	311
25°	884	400
35°	483	301
45°	149	121
55°	35	34
65°	10	11
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P211590

CATALOG NUMBER: LSR4B20D010BZ EC4B10209030 4LBMH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1289.9
2.5°	1282.0
5°	1266.3
7.5°	1236.9
10°	1199.6
12.5°	1154.4
15°	1111.2
17.5°	1062.1
20°	1009.1
22.5°	952.2
25°	883.5
27.5°	801.0
30°	704.8
32.5°	596.8
35°	483.0
37.5°	376.9
40°	282.7
42.5°	208.1
45°	149.2
47.5°	102.1
50°	70.7
52.5°	49.1
55°	35.3
57.5°	25.5
60°	19.6
62.5°	13.7
65°	9.8
67.5°	7.9
70°	5.9
72.5°	3.9
75°	2.0
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)